



# Locking castor with mounting plate

For loads up to 1000kg

RIM



- A combination of a swivel castor and an adjustable locking support
- Used to easily support and moving machines or other heavy equipment and then positioning them in a very stable manner.
- Installation starts by lowering the locking support using a nut.
- With the wheel no longer resting on the ground, the supported unit can be levelled despite any irregularities in the floor.
- Operating temperature range: -30 to +80°C



## Materials

- Polyamide central control cross nut
- Anti-skid rubber mount allowing absorption of vibration and noise
- Body: Moulded cast aluminium body, hammered ivory paint finish
- Swivel system provided by 2 ball rings
- Mounting plate has a threaded central hole, threaded rod and nut supplied.
- Wheel: Black polyamide Shore D 70

Adjusting nut



## DISCOUNTS

Qty	1+	5+	14+
Disc.	List	-5%	On request

Part number	ØA	B	H1	H2	L	M	ØT	Swivel interference ØK	Load (kg)	Price each 1 to 5
RIM42-60/PLE	42	20	71	81	55x55	42x42	6,5	84	60	44.77 €
RIM50-280/PLE	50	25	82	92	73x73	58x58	7	101	280	71.10 €
RIM63-550/PLE	63	28	103	118	90x90	70x70	9	125	550	96.62 €
RIM75-800/PLE	75	30	120	132	95x95	70x70	11	142	800	106.81 €
RIM75-1000/PLE	75	30	120	132	95x95	70x70	11	142	1000	127.36 €

Dimensions in mm

**0 825 88 6000**  
 Service 0,15 € / min  
 + prix appel

Fax

## Altri prodotti...



BPHR  
Sfera portante, Forte



ACLLPP  
Sistema di chiusura,  
Chiusura a molla



CHAEss  
Cerniera estetica, Inox



PLC\_PLT  
Magnete, Con foro  
maschiato



PGB  
Attrezzi, Porta attrezzi



BAC110  
Contenitore a becco,  
Aggancio orientabile



NSR  
Connettore rinvio  
d'angolo, Regolabile



SBF  
Sealed flange bearing  
unit for Food Industry,  
cover



PTA50ssEB  
Piede snodato con  
base stampata Ø50,  
4000N



STRIP1000  
Spazzola strip,  
Lunghezza 1m



BPHF  
Sfera portante a  
incastro con flangia,  
Forte



YG2  
Ingranaggio dritto  
PRESTAZIONE, Acciaio  
35NCD6

## Prodotti correlati



RIMtce  
Ruota di livellamento,  
Con foro centrale



PDR-RD  
Piede con ruota  
integrata, Ruota  
disassata