

# Polyamide castor with central hole


For heavy loads up to 600kg

RPCTC

- Industrial wheel suitable for loads up to 600kg
- Swivel system uses two ball races
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Smooth central bore
- Materials:
  - Top plate: pressed steel sheet, protected by bright zinc plating
  - Polyamide wheel (see RPC)
  - Working temperature range: - 30°C to + 80°C

## Advantages

- Light
- Will not mark or stain floor
- Low rolling resistance
- For solid, hard floors



## DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	ØE	Swivel interference ØK	Max load (kg)	Price each 1 to 9
<b>Swivel</b>							
RPC60/TC/P	60	31	97	12	140	200	8,74 €
RPC80/TC/P	80	32	106	12	160	250	9,28 €
RPC100/TC/P	100	32	124	12	184	300	9,72 €
RPC125/TC/P	125	36	152	12	210	350	14,47 €
RPC150/TC/P	150	37	181	12	246	400	20,32 €
RPC160/TC/P	160	40	189	12,5	268	500	41,09 €
RPC200/TC/P	200	50	232	12,5	318	600	47,24 €
<b>Swivel with double brake</b>							
RPC80/TC/PDB	80	32	106	12	290	250	14,64 €
RPC100/TC/PDB	100	32	124	12	290	300	15,37 €
RPC125/TC/PDB	125	36	152	12	290	350	19,53 €
RPC150/TC/PDB	150	37	181	12	290	400	25,66 €
RPC160/TC/PDB	160	40	189	12,5	268	500	51,83 €
RPC200/TC/PDB	200	50	232	12,5	318	600	53,78 €

Dimensions in mm

**0 825 88 6000**  
Service 0,15 € / min  
+ prix appel

Fax


cial2@hpceurope.com

**HPC**

SUPPLEMENT 2019

267

## Altri prodotti...



Inserti filettati, Inox



Manicotto di riduzione, Cilindrico - acciaio



Angolare, 8 fori



Sfera portante con flangia, Leggero



Perno di fissaggio, con chiusura a scatto



Giunto a soffietto Gerwah®, da 0.5 a 12Nm



Guida su semi-binari, Boccola di regolazione



Rotex®, elastico, acciaio



Ruota di rinvio, Serie 882



Ingranaggio elicoidale ad assi incrociati



Coppia ruota e vite senza fine, Acciaio



Cuscinetto obliquo a sfere, Acciaio

## Prodotti correlati



Ruota girevole a foro centrale, Inox - Poliammide



Stem support for caster, For swivel caster with central hole



Ruota, Poliammide



Ruota girevole a foro centrale, Acciaio - Poliammide - a doppio bloc...