

Spacer for index bolt

SLBE

Used with SLB and SLBS




- Allows the length of the thread of index bolts to be adapted to the length required for an application (wall thickness)
- Material:
stainless steel, natural finish

Accessories

- Used with SLB and SLBS index bolts
SLB and SLBS

Info

- Not sold individually,
contact us for details



DISCOUNTS

Qty	1+	40+	100+	200+
Disc.	List	-5%	-10%	On request

Part number	ØD	ØD1	Length L (mm)	Weight (kg)	Price each 1 to 39
SLBE8-11-2/SS	8	11	2	0,6	0,59 €
SLBE8-11-3/SS	8	11	3	0,9	0,62 €
SLBE8-11-4/SS	8	11	4	1,3	0,68 €
SLBE8-11-6/SS	8	11	6	2,0	0,72 €
SLBE8-11-8/SS	8	11	8	2,6	0,78 €
SLBE10-14-2/SS	10	14	2	1,1	0,62 €
SLBE10-14-3/SS	10	14	3	1,7	0,72 €
SLBE10-14-4/SS	10	14	4	2,2	0,72 €
SLBE10-14-6/SS	10	14	6	3,4	0,78 €
SLBE10-14-8/SS	10	14	8	4,5	0,87 €
SLBE12-15-2/SS	12	15	2	0,9	0,68 €
SLBE12-15-4/SS	12	15	4	1,9	0,78 €
SLBE12-15-5/SS	12	15	5	2,4	0,84 €
SLBE12-15-6/SS	12	15	6	2,8	0,87 €
SLBE12-15-8/SS	12	15	8	3,8	0,97 €
SLBE12-17-2/SS	12	17	2	1,6	0,78 €
SLBE12-17-4/SS	12	17	4	3,4	0,87 €
SLBE12-17-5/SS	12	17	5	4,3	0,97 €
SLBE12-17-6/SS	12	17	6	5,2	1,00 €
SLBE12-17-8/SS	12	17	8	6,9	1,08 €
SLBE16-21-4/SS	16	21	4	4,4	1,00 €
SLBE16-21-5/SS	16	21	5	5,5	1,08 €
SLBE16-21-6/SS	16	21	6	6,6	1,17 €
SLBE16-21-8/SS	16	21	8	8,8	1,26 €
SLBE16-21-10/SS	16	21	10	11,0	1,32 €

Dimensions in mm

Altri prodotti...



SHTC
Tavola lineare
Drylin®, Nessuna
manutenzione



STC
Deceleratore, Ghiera
d'arresto



R204
Molla per stampi
ISO10243, Medio



DKGS
Giunto senza gioco
Gerwah®, da 0.5 a
3Nm



PML
Piede massiccio per
carichi pesanti, Ø 100,
120 o 150



PV2R
Braccio portaventosa
orientabile, Serraggio
rinforzato



SSDB
Ingranaggio conico
inox, 2:1



ZA
Albero per guida
lineare, Acciaio
temprato




CLSCLP_SS
Perno serie corta inox,
Inox - serie corta



RPCplss
Ruota girevole a
doppio bloccaggio,
Inox - poliammide



VTHbr
Vite a testa esagonale
- DIN933, Ottone



CXS
Anello di arresto
esterno DIN471,
esterno DIN 471

Prodotti correlati



SLB
Pistoncino a molla,
acciaio classe 5.8



SLB
Pistoncino a molla,
acciaio classe 5.8



SLB
Pistoncino a molla,
acciaio classe 5.8



SLB
Pistoncino a molla,
acciaio classe 5.8