

TIF

Stainless steel A2

- **Conforms to DIN 975**
- **Material:**
Stainless steel: 303/304 - A2
- **Working temperature up to +430°C**

Uses


- Suitable for harsh environments

Options

- Stainless steel 316

Accessories

- Nuts **SHN**
- Stainless steel screws



DISCOUNTS

| | | | | |
|------------|------|------|------------|-----|
| Qty. | 1+ | 6+ | 20+ | 40+ |
| Disc. List | -15% | -20% | On request | |

| Part number | Thread | Pitch | Length (mm) | Stock* | Price each 1 to 5 |
|-------------|--------|-------|-------------|--------|-------------------|
| TIF-2/SS | M2 | 0,40 | 1000 | ✓ | 9,39 € |
| TIF-2.5/SS | M2,5 | 0,45 | 1000 | ✓ | 10,31 € |
| TIF-3/SS | M3 | 0,50 | 1000 | ✓ | 3,74 € |
| TIF-4/SS | M4 | 0,70 | 1000 | ✓ | 3,72 € |
| TIF-5/SS | M5 | 0,80 | 1000 | ✓ | 2,58 € |
| TIF-6/SS | M6 | 1,00 | 1000 | ✓ | 2,84 € |
| TIF-8/SS | M8 | 1,25 | 1000 | ✓ | 5,34 € |
| TIF-10/SS | M10 | 1,50 | 1000 | ✓ | 8,57 € |
| TIF-12/SS | M12 | 1,75 | 1000 | ✓ | 12,39 € |
| TIF-14/SS | M14 | 2,00 | 1000 | ✓ | 17,04 € |
| TIF-16/SS | M16 | 2,00 | 1000 | ✓ | 20,71 € |
| TIF-18/SS | M18 | 2,50 | 1000 | ✓ | 30,29 € |
| TIF-20/SS | M20 | 2,50 | 1000 | ✓ | 33,72 € |
| TIF-22/SS | M22 | 2,50 | 1000 | - | 44,78 € |
| TIF-24/SS | M24 | 3,00 | 1000 | - | 48,29 € |
| TIF-27/SS | M27 | 3,00 | 1000 | - | 73,40 € |
| TIF-30/SS | M30 | 3,50 | 1000 | - | 92,83 € |
| TIF-33/SS | M33 | 3,50 | 1000 | - | 118,04 € |
| TIF-36/SS | M36 | 4,00 | 1000 | - | 125,44 € |

*Depending on availability

Altri prodotti...



CHM40

Riduttore a ruota e vite senza fine, fino a 57 Nm



FF20

Riduttore ad alberi paralleli, da 5.80 a 23 Nm



ZDB

Ingranaggio conico in plastica, 2:1



G0

Ingranaggio dritto acciaio, Acciaio 20NCD2



ZHBRA

Ingranaggio conico in plastica, 1,25:1 2:1 3:1




SBF

Sealed flange bearing unit for Food Industry, cover



PRF_GAL

Rotella per profilo alluminio, Rotella liscia



B

Ingranaggio conico - Acciaio 60C40, 1:1



GE_ES

Snodo sferico, acciaio/acciaio



BOX-TOR-A

Valigetta di guarnizioni toriche in



PPS

Anello di sollevamento, Gancio



PLB

Distanziatore cilindrico, Ottone

Prodotti correlati



SHN

Dado esagonale - DIN934, Inox A2



SHW

Rondella semplice, Inox A2



MCL

Manicotto cilindrico maschiato, Cilindrico - inox



MHX

Manicotto esagonale maschiato, Esagonale - inox