


- **Dual threaded screw wood/metal**
- Allows a metal object to be fixed to wood
- Materials:
  - Galvanised steel
  - Stainless steel, 304
- Supplied by the pack




### Mounting

- Screw should first be inserted into the wood using a suitable spanner
- Compatible with **N, SHN, NINA** and **NIN** nuts



Typical application



### DISCOUNTS Steel

Qty	1+	6+	20+	50+
Disc.	List	-10%	-20%	On request

### DISCOUNTS S/steel

Qty	1+	6+	10+
Disc.	List	-5%	On request

Part number	Part number		ØF	L	Qty per pack		Price each 1 to 5	
	Steel	Stainless steel			Steel	S/steel	Steel	S/steel
VCMB5-40/B		-	M5	40	100	-	5,65 €	-
VCMB5-50/B		-	M5	50	100	-	9,36 €	-
VCMB6-60/B	VCMB6-60/SS/B		M6	60	100	100	11,00 €	36,38 €
VCMB6-80/B	VCMB6-80/SS/B		M6	80	100	100	18,18 €	45,69 €
VCMB6-100/B	VCMB6-100/SS/B		M6	100	100	100	29,76 €	61,45 €
VCMB6-120/B	VCMB6-120/SS/B		M6	120	100	100	30,83 €	69,20 €
VCMB8-50/B	VCMB8-50/SS/B		M8	50	100	100	11,75 €	96,98 €
VCMB8-60/B	VCMB8-60/SS/B		M8	60	100	100	12,67 €	57,14 €
VCMB8-80/B	VCMB8-80/SS/B		M8	80	100	50	16,68 €	38,27 €
VCMB8-100/B	VCMB8-100/SS/B		M8	100	100	50	20,78 €	51,87 €
VCMB8-120/B	VCMB8-120/SS/B		M8	120	100	50	25,32 €	60,40 €
VCMB8-140/B	VCMB8-140/SS/B		M8	140	100	50	32,73 €	70,23 €
VCMB8-160/B	VCMB8-160/SS/B		M8	160	100	50	36,56 €	69,36 €
VCMB10-60/B		-	M10	60	100	-	22,32 €	-
VCMB10-80/B	VCMB10-80/SS/B		M10	80	50	25	15,42 €	46,74 €
VCMB10-100/B	VCMB10-100/SS/B		M10	100	50	25	18,88 €	39,09 €
VCMB10-120/B	VCMB10-120/SS/B		M10	120	50	25	33,04 €	46,29 €
VCMB10-140/B	VCMB10-140/SS/B		M10	140	50	25	42,18 €	50,57 €

Dimensions in mm

## Altri prodotti...



G-ECO  
Ingranaggio dritto  
acciaio - serie ECO,  
Acciaio C45



AC144  
Piastrina di riscontro  
piatta per chiusura,  
22mm



RJA10\_03  
Guarnizione in  
gomma, Da  
agganciare




CMM  
Testa a snodo  
maschio DIN  
ISO12240-4, Acciaio /  
bronzo



MSP38  
Inserto con piastrina a  
incollare  
Masterplate®,  
Cilindrico Ø38 con...



BTE  
Tenditore automatico  
universale, Per  
applicazioni correnti



PTBss  
Bullone a occhiello  
inox, Inox



DILC  
Indexing plunger with  
cam, with cam



ATZYSS  
Antivibrante elastico  
inox sgolato, Inox



CNA-CNG  
Staffa di montaggio  
per molla a gas,  
Staffa di montaggio a



SHN  
Dado esagonale -  
DIN934, Acciaio (Class  
6/8J)



RPCplss  
Ruota girevole con  
piastra, Inox -  
Poliammide

## Prodotti correlati



VCMB  
Vite di giunzione  
metallo/legno, Acciaio



SHN  
Dado esagonale -  
DIN934, Inox A2



NIN  
Dado autofrenante ,  
Inox A2



SHW  
Rondella semplice ,  
Inox A2