



- **Wing screw for use with Hygienic Usit® safety washers**
- The wing screw makes perfect screw connections extremely easy.
- They can be easily opened or re-tightened without tools.
- Generous rounded form
- Fully polished surface, roughness less than Ra 0.8µm
- Material:
Stainless steel 1.4404 (316L)
Polished mirror finish




Advantages

- Ideal for use in areas where there is contact with the product or inside aseptic isolators.
- Regardless of the mounting position of the wing screw, dirt and residue from products or cleaning materials will not be retained. This guarantees easy cleaning.
- The base of the wing screw is specially designed for an almost cavity-free seal of the screwed connection thus meeting hygiene requirements.

Accessory

- RDE sealing washer (see pages 37 à 39)



DISCOUNTS

Qty	1+	5+	10+	25+
Disc	Prix	-5%	-10%	On request

Part N°	ØD	ØD2	A	H	H1	B	R	L	L1	Price each
										1 to 4
VPR-4/HUSS	M4	10,8	20	19	5,3	4	0,45	8	7	19,18 €
VPR-5/HUSS	M5	11,8	21	21	6,0	5	0,50	10	9	20,19 €
VPR-6/HUSS	M6	14,2	25	25	7,0	6	0,55	12	11	22,57 €
VPR-8/HUSS	M8	18,0	33	33	8,4	8	0,60	16	15	30,25 €
VPR-10/HUSS	M10	22,3	40	40	10,0	10	0,75	20	19	47,90 €

All dimensions in mm

Altri prodotti...



G4

Ingranaggio dritto
acciaio , Acciaio
20NCD2



S2B

Supporto corto per
manicotto chiuso a
sfere, Chiuso - Corto



NSO

Supporto standard per
manicotto aperto a
sfere, Aperto - lungo



HBM

Guida su semi-binari,
Boccola di regolazione



MEB

Ingranaggio conico in
plastica stampata, 1:1



M1

Vite senza fine ,
Acciaio non temprato



UTKpwc

Guida lineare
Utilitrack®, Ruota a V
- rivestimento
polimero



PO

Maniglia a ponte -
Multi-settore, Foro
cieco maschiato




MFB_MHB

Ingranaggio conico in
plastica stampata ,
1.5:1



H0

Ingranaggio elicoidale
ad assi incrociati a
90°, Plastica lavorata
...



RPP8


Cinghia di
trasmissione RPP,
RPP8



VDSCB

Bloccaggio scorrevole
per la regolazione,
Piastrini di base per il
blo...

Prodotti correlati



RDE-W

Rondella di tenuta
Hygienic Usit®, Inox -
EPDM bianco



RDE-B

Rondella di tenuta
Hygienic Usit®,
Stainless steel - EPDM
blu