# Welded lifting ring for straight lifts New Stock

## ASH

Steel

- ***Weldable lifting ring***
- *Marked with CE symbol, CMU and manufacturer's ref*
- *Material:*
  *Black unfinished steel*





### Assembly


- *Installation instructions available on request*
- *Welding should be done in accordance with DIN 5817 (section 15 429) by an operator qualified to EN287-1*

### Info.

- *The breaking load is obtained by multiplying the SWL by a factor of safety of 5.*



Typical application




### DISCOUNTS

| Qty | 1+ | 6+ | 20+ | 50+ |
|---|---|---|---|---|
| Disc. | List | -10% | -20% | On request |

| Part number | CMU (kg) | ØT | ØA | B | C | D | Weight (kg) | Stock* | Price each 1 to 5 |
|---|---|---|---|---|---|---|---|---|---|
| ASH24-200 | 200 | 9 | 24 | 43 | 10 | 54 | 0,06 | ✔ | 2,07 € |
| ASH31-500 | 500 | 12 | 31 | 55 | 12 | 68 | 0,14 | ✔ | 2,97 € |
| ASH43-1000 | 1000 | 13 | 43 | 67 | 12 | 85 | 0,18 | ✔ | 4,45 € |
| ASH48-2000 | 2000 | 18 | 48 | 82 | 16 | 105 | 0,40 | ✔ | 6,92 € |
| ASH57-3000 | 3000 | 21 | 57 | 95 | 17 | 128 | 0,66 | - | 13,19 € |
| ASH67-4000 | 4000 | 25 | 67 | 107 | 15 | 148 | 1,02 | - | 25,10 € |
| ASH82-6000 | 6000 | 28 | 82 | 135 | 24 | 189 | 1,92 | - | 78,00 € |
| ASH100-8000 | 8000 | 30 | 100 | 165 | 35 | 210 | 3,12 | - | 81,93 € |

**Depending on availability - Dimensions in mm*

# Welded lifting ring for 45° lifts

## Steel

## ASL

- ***Weldable lifting ring***
- *Marked with CE symbol, CMU and manufacturer's ref*
- *Material:*
  *Black unfinished steel*

### Assembly


- *Installation instructions available on request*
- *Welding should be done in accordance with DIN 5817 (section 15 429) by an operator qualified to EN287-1*

### Info.


- *The breaking load is obtained by multiplying the SWL by a factor of safety of 5.*



NUOVO !



Typical application




### DISCOUNTS

| Qty | 1+ | 6+ | 20+ | 50+ |
|---|---|---|---|---|
| Disc. | List | -10% | -20% | On request |

| Part number | CMU (kg) | ØT | ØA | B | C | D | E | Weight (kg) | Stock* | Price each 1 to 5 |
|---|---|---|---|---|---|---|---|---|---|---|
| ASL31-500 | 500 | 12 | 31 | 55 | 13 | 89 | 82 | 0,16 | ✔ | 3,55 € |
| ASL42-1000 | 1000 | 14 | 42 | 69 | 13 | 113 | 101 | 0,30 | ✔ | 4,53 € |
| ASL45-2000 | 2000 | 18 | 45 | 81 | 18 | 134 | 123 | 0,50 | ✔ | 9,42 € |
| ASL57-3000 | 3000 | 21 | 57 | 97 | 19 | 152 | 140 | 0,80 | - | 15,81 € |
| ASL65-4000 | 4000 | 24 | 65 | 113 | 23 | 167 | 155 | 1,24 | - | 26,15 € |
| ASL83-6000 | 6000 | 28 | 83 | 140 | 31 | 218 | 205 | 2,36 | - | 65,55 € |

**Depending on availability - Dimensions in mm*