

# Motoriduttore inox a ruota e vite senza fine

Componete il vostro motoriduttore\*

Ideale per le applicazioni  
agroalimentari



Piedi di supporto  
**RFV-FP**



Coperchio di protezione  
chiuso **RFV-CAP**



Motore da 0.18 kW a 1.5 kW



Riduttore **RFV40, RFV50 o RFV63**,  
Rapporto di riduzione da 7,5/1 a 100/1  
3 flange a scelta a seconda del motore  
scelto



Coperchio di protezione  
**RFV-CAP** aperto o chiuso per  
evitare la ritenzione di sporco  
nell'alesaggio in uscita



Braccio di reazione  
**RFV-BR** per sostenere  
meglio il carico

\*Vedere la tabella di selezione

# Stainless steel asynchronous motor, 0.18kW

Torque up to 3,49Nm

DER63

## Three-phase asynchronous motor ideal for the food industry

- B14 or B5 flange
- 4-pole motor
- No-load speed 1,420 rpm
- Voltage 230/400V AC
- Rounded and polished surfaces to avoid material retention
- Closed housing, without ventilation
- Hermetically sealed junction box
- IP66 protection
- Insulation class ISO F
- Material:  
304 stainless steel housing

stainless steel



B5 or B14 flange




Designed for the food industry

## Accessories

- RFV and RFK gearboxes (to create a motorised gearbox)

## Option

- Motor with B3 flange



## Flange dimensions

	Flange	ØR	ØP	ØM	ØN
DER63-A4-B14/SS	B14	M5	90	75	60
DER63-A4-B5/SS	B5	10	140	115	95

## DISCOUNTS

Qty	1+	2+	4+
Disc.	Net -5%	On request	On request

Part N°	L	Power (kW)	Current (A)	Efficiency	Power factor	Torque				Weight (kg)	Unit price
						Tn (Nm)	Ts (Nm)	Tmax (Nm)	Is (A)		
<b>B14 flange</b>											
DER63-A4-B14/SS	237	0,18	0,55	69,9%	0,68	1,21	2,54	2,66	2,42	8,7	589,24 €
<b>B5 flange</b>											
DER63-A4-B5/SS	237	0,18	0,55	66,9%	0,68	1,21	2,54	2,66	2,42	8,7	664,71 €

Fax

0 825 88 6000

Service 0,15 € / min  
+ prix appel

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

23