

# Motoriduttore inox a ruota e vite senza fine

Componete il vostro motoriduttore\*

Ideale per le applicazioni  
agroalimentari



Piedi di supporto  
**RFV-FP**



Coperchio di protezione  
chiuso **RFV-CAP**



Motore da 0.18 kW a 1.5 kW



Riduttore **RFV40, RFV50 o RFV63**,  
Rapporto di riduzione da 7,5/1 a 100/1  
3 flange a scelta a seconda del motore  
scelto



Coperchio di protezione  
**RFV-CAP** aperto o chiuso per  
evitare la ritenzione di sporco  
nell'alesaggio in uscita



Braccio di reazione  
**RFV-BR** per sostenere  
meglio il carico

\*Vedere la tabella di selezione

# Stainless steel asynchronous motor, 0.55 - 0.75kW

Torque up to 17,46Nm

DER80

## - Three-phase asynchronous motor ideal for the food industry

- B14 flange
- 4-pole motor
- No-load speed 1,440 rpm
- Voltage 230/400V AC
- Rounded and polished surfaces to avoid material retention
- Closed housing, without ventilation
- Hermetically sealed junction box
- IP66 protection
- Insulation class ISO F
- Material:  
304 stainless steel housing

stainless steel



B14 flange





## Accessories

- RFV and RFK gearboxes (to create a motorised gearbox)

## Option

- Motor with B5 flange

Designed for the food industry



## DISCOUNTS

Qty	1+	2+	4+
Disc.	Net -5%	On request	

Part N°	L	Power (kW)	Current (A)	Efficiency	Power factor	Torque				Weight (kg)	Unit price
						Tn (Nm)	Ts (Nm)	Tmax (Nm)	Is (A)		
DER80-A4-B14/SS	308	0,55	1,29	81,8%	0,75	3,65	87,6	8,9	6,71	17,6	804,55 €
DER80-B4-B14/SS	348	0,75	1,76	84,4%	0,74	4,91	11,29	11,29	10,56	21,0	903,30 €

All dimensions in mm

**0 825 88 6000**  
Service 0,15 € / min  
+ prix appel

cial2@hpceurope.com

**HPC** SUPPLEMENT 2019

25