

- Manual indexing button, smooth body, no flange

- Two versions available.

- Material :

Body: Steel 1.0403 (suitable for welding)


Pin: Hardened steel, Resistance class 5.

Head: Dark grey thermosetting plastic


Info.

- Index bolts are used where lateral movement is required to be blocked. Pulling the handle releases the pin. The M version allows the pin to be held in the retained position.

- Bolts should be welded using a WIG inert gas process.



“L” type
without
retaining
mechanism



“M” type
without
retaining
mechanism

DISCOUNTS

| | | | |
|-------|----------------------|----|-----|
| Qty. | 1+ | 6+ | 20+ |
| Disc. | List -10% On request | | |

| Part number | ØD | ØD1 | ØD2 | L | L1 | H | Fx30° | Spring force | | Price each 1 to 5 |
|-------------|----|-----|-----|------|----|----|-------|--------------|-----------|----------------------|
| | | | | | | | | Initial (N) | Final (N) | |
| SLBW10-L | 4 | 10 | 18 | 38,5 | 21 | 4 | 1,0 | 6 | 12 | 7,27 € |
| SLBW10-M | 4 | 10 | 18 | 38,5 | 21 | 4 | 1,0 | 6 | 12 | 9,33 € |
| SLBW12-L | 5 | 12 | 21 | 43,5 | 24 | 5 | 1,3 | 5 | 12 | 6,90 € |
| SLBW12-M | 5 | 12 | 21 | 43,5 | 24 | 5 | 1,3 | 5 | 12 | 8,88 € |
| SLBW14-L | 6 | 14 | 25 | 51,7 | 28 | 6 | 1,8 | 6 | 14 | 7,66 € |
| SLBW14-M | 6 | 14 | 25 | 51,7 | 28 | 6 | 1,8 | 6 | 14 | 9,83 € |
| SLBW18-L | 8 | 18 | 33 | 68,0 | 36 | 8 | 2,3 | 15 | 35 | 9,90 € |
| SLBW18-M | 8 | 18 | 33 | 68,0 | 36 | 8 | 2,3 | 15 | 35 | 11,67 € |
| SLBW22-L | 10 | 22 | 33 | 74,0 | 40 | 10 | 2,8 | 15 | 40 | 15,18 € |
| SLBW22-M | 10 | 22 | 33 | 74,0 | 40 | 10 | 2,8 | 15 | 40 | 17,81 € |