

Mounting feet with integrated castors

PDR

Centre castor


- Combines the advantages of a static mounting foot and a castor
- Use a hexagonal spanner to release the castor
- Castor protrudes 12.5mm when released
- Only for use on surfaces that are smooth (crevices less than 5mm) and horizontal (max slope 3°)
- Max static load 2,500 kg per foot
- Max load 200 kg per foot if used in movable mode
- Materials:
 - Base - Polyamide
 - Sole - NBR rubber
 - Threaded shaft - Chromed steel

Typical application


- A vessel remains static whilst the product within is processed but once empty, can be moved for cleaning purposes.

Advantages

- Flexibility (1 item performs 2 functions)
- Less manoeuvring to move a structure
- Time saving



Retracting the castor



DISCOUNTS

Qty	1+	6+	10+
Disc.	List	-5%	On request

Part number	ØM	L	Load Castor fixed (static) (kg)	Load Castor free (dynamic) (kg)	Price each 1 to 5
With threaded shaft					
PDR100-16-50/RC	M16	50	2500	200	112,67 €
PDR100-16-100/RC	M16	100	2500	200	116,07 €
PDR100-20-75/RC	M20	75	2500	200	116,07 €
PDR100-20-125/RC	M20	125	2500	200	119,50 €
PDR100-24-75/RC	M24	75	2500	200	116,07 €
PDR100-24-125/RC	M24	125	2500	200	119,50 €
With 80x80mm mounting plate					
PDR100-80-80/RC	4x8.5mm holes		2500	200	116,07 €

Dimensions in mm