

Anti-vibration machine mount

New

PMB

Format Oval base plate

- With 2 fixing holes
- Loads shown refer to permissible static vertical dead load
- Materials :
Natural rubber
Steel structure

NEW !






Application

- These elements are ideal for low frequencies because the rubbers are available with different hardnesses so that a wide load range can be covered

Info.

- Supplied with support disc for better load distribution



DISCOUNTS

Qty	1+	6+	10+	20+
Disc.	List	-5%	-10%	On request

Part number	ØD	H1	H	E	L	ØM	ØA	S	Hardness shore	Load max (daN)	Deflexion	Price each 1 to 5
PMB40-M6-35	40	18	20	52	64	M6	6,2	2	35	2,5	2,5±0,5	9,83 €
PMB40-M6-45	40	18	20	52	64	M6	6,2	2	45	5	2,5±0,5	9,83 €
PMB40-M6-60	40	18	20	52	64	M6	6,2	2	60	10	2,5±0,5	9,83 €
PMB60-M6-45	60	22	24	76	90	M6	6,2	2	45	15	3,5±0,5	17,04 €
PMB60-M6-60	60	22	24	76	90	M6	6,2	2	60	25	3,5±0,5	17,04 €
PMB60-M6-75	60	22	24	76	90	M6	6,2	2	75	50	3,5±0,5	17,04 €
PMB80-M8-45	80	25	27	100	120	M8	8,2	2	45	40	4,5±0,5	23,19 €
PMB80-M8-60	80	25	27	100	120	M8	8,2	2	60	80	4,5±0,5	23,19 €
PMB80-M8-75	80	25	27	100	120	M8	8,2	2	75	120	4,5±0,5	23,19 €
PMB100-M10-45	100	25	28	124	148	M10	10,2	2,5	45	75	4,5±1	30,37 €
PMB100-M10-60	100	25	28	124	148	M10	10,2	2,5	60	160	4,5±1	30,37 €
PMB100-M10-75	100	25	28	124	148	M10	10,2	2,5	75	220	4,5±1	30,37 €
PMB150-M14-45	150	35	40	182	214	M14	11,8	4	45	130	7±1,5	66,64 €
PMB150-M14-60	150	35	40	182	214	M14	11,8	4	60	300	7±1,5	66,64 €
PMB150-M14-75	150	35	40	182	214	M14	11,8	4	75	400	7±1,5	66,64 €

Dimensions in mm

HPC

WEB
04/2024

www.hpceurope.com

Tel. +33(0)4 37 496 496