







**- Materiale:**

- Alluminio anodizzato duro
- Lunghezza standard: 1.000mm
- Opzione: possibile fino a 4.000mm
- Per carrello **WJUM10** e **WJRM10**



**Modulabile**



### SCONTI PER QUANTITÀ

Qtà	1+	5+	10+	15+	20+
Sc.	Prezzo	-10%	-15%	-20%	Su richiesta

Codice	Lunghezza L (mm)	Lunghezza L max. (mm)	C5 mini	C5 max.	ly (mm <sup>4</sup> )	lz (mm <sup>4</sup> )	Wby (mm <sup>3</sup> )	Wbz (mm <sup>3</sup> )	Massa (kg/m)	Prezzo unit. da 1 a 4
WS10	1000	4000	20	79,5	19000	2850	1000	310	0,62	✓ 70,03 €
WS10-40	1000	4000	20	79,5	91000	5100	3600	590	1,00	✓ 102,89 €
WS10-80	1000	4000	20	79,5	388000	6100	9200	650	1,50	✓ 171,38 €

\*Nei limiti delle disponibilità - Dimensioni in mm