

Hinge for aluminium profile

ACL-CHARJ

Adjusts in 2 directions




- Hinge that can be adjusted in 2 directions
- Allows precise positioning, both horizontally and vertically
- Materials:
Plates – Moulded zinc
Pin- stainless steel

Advantages

- This hinge can be adjusted in both the X and Y planes thanks to use of serrated oblong holes and serrated washers

Use

- Use M6 FHC screws (not supplied)
See **FHC6-16/SS** (Vol 1, page 427)
and **PRF-ECL-M6/SS** (Vol 5, page 323)



DISCOUNTS

Qty	1+	50+	100+
Disc	Net	+5%	On request

Part N°	Load FA max (N)	Load FR max (N)	Weight (g)	Stock*	Price each 1 to 49
Ajustable dans 2 directions					
ACL-CHARJ60-76	1200	2200	190	-	26,92 €


Altri prodotti...



PM3
Vite senza fine,
Acciaio non temprato



PSG15
Ingranaggio dritto di
precisione, Inox 303



B
Ingranaggio conico -
Acciaio 60C40, 1:1



TBV
Tavola di
posizionamento
verticale manuale,
7kg



APBC
Supporto per sensore,
Tubo di collegamento
per morsetto



ACL-PL
Elementi di giunzione,
Piastra di fissaggio -
86x86 mm



PDD
Pressore a molla
sensore di
rilevamento, Con asta
di comando per int...



ETP
Maniglia e battuta per
porta, Modulare



ECF
Rivetto rivestito in
gomma di fissaggio,



PW_PWG05
Vite senza fine di
precisione, Inox



BEAB
Manopola, stella,
antibatterico



MDR_SS
Grillo con chiodo ad
occhiello, Inox

Prodotti correlati



FHCSS
Vite a testa svasata
piana, Inox A2 - DIN
7991



PRF_ECL
Fissaggio, Dado
quadrato con
linguetta - Inox



PRF4545
Profilato alluminio
standard, 45 x 45 mm