



Locking castor with mounting plate

For loads up to 1000kg

RIM



- A combination of a swivel castor and an adjustable locking support
- Used to easily support and moving machines or other heavy equipment and then positioning them in a very stable manner.
- Installation starts by lowering the locking support using a nut.
- With the wheel no longer resting on the ground, the supported unit can be levelled despite any irregularities in the floor.
- Operating temperature range: -30 to +80°C



Adjusting nut

Materials

- Polyamide central control cross nut
- Anti-skid rubber mount allowing absorption of vibration and noise
- Body: Moulded cast aluminium body, hammered ivory paint finish
- Swivel system provided by 2 ball rings
- Mounting plate has a threaded central hole, threaded rod and nut supplied.
- Wheel: Black polyamide Shore D 70



DISCOUNTS

Qty	1+	5+	14+
Disc.	List	-5%	On request

Part number	ØA	B	H1	H2	L	M	ØT	Swivel interference ØK	Load (kg)	Price each 1 to 5
RIM42-60/PLE	42	20	71	81	55x55	42x42	6,5	84	60	44.77 €
RIM50-280/PLE	50	25	82	92	73x73	58x58	7	101	280	71.10 €
RIM63-550/PLE	63	28	103	118	90x90	70x70	9	125	550	96.62 €
RIM75-800/PLE	75	30	120	132	95x95	70x70	11	142	800	106.81 €
RIM75-1000/PLE	75	30	120	132	95x95	70x70	11	142	1000	127.36 €

Dimensions in mm

0 825 88 6000

Service 0,15 € / min
+ prix appel

Fax

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

283