

Locking pin with interlocking safety latch

Steel

AFSE


- Allows easy and quick location of parts or workpieces requiring assembly

- Material:


Galvanized steel

Advantages

- The interlocking safety latch allows components with a large cross sectional area to be secured together
- In addition they absorb any axial movement
- Indexing slots in the safety latch are used to locate the "Closed" and "Open" position



Typical application



DISCOUNTS

Qty	1+	6+	10+	25+
Disc.	List	-5%	-10%	On request

Part number	ØD	ØD1	L	L1	L2	H	B	B1	Mounting hole H11	Shearing force		Price each 1 to 5
										double section max (kN)	Extraction force (N)	
AFSE6-25	12	6	25	31	45	3	16,9	2	6	12	190	15,42 €
AFSE6-40	12	6	40	46	60	3	16,9	2	6	12	190	15,75 €
AFSE6-50	12	6	50	56	70	3	16,9	2	6	12	190	16,23 €
AFSE8-25	16	8	25	31	46	4	16,9	2	8	21	270	16,23 €
AFSE8-40	16	8	40	46	61	4	16,9	2	8	21	270	16,71 €
AFSE8-50	16	8	50	56	71	4	16,9	2	8	21	270	17,01 €

Dimensions in mm

0 825 88 6000
 Service 0,15 € / min
 + prix appel

Altri prodotti...



DB

Ingranaggio conico -
Acciaio 60C40, 2:1



RFV63

Riduttore inox a ruota
e vite senza fine, fino
a 152 Nm




ZHBRA

Ingranaggio conico in
plastica, 1,25:1 2:1
3:1



FRss

Inseri filettati, Inox



CXS

Anello di arresto
esterno DIN471,
esterno DIN 471



INO

Ingranaggio interno,
Plastica lavorata
(delrin)



PTA80

Piede snodato con
base stampata Ø80,
10000N



PX_PO

Maniglia -
movimentazione
manuale, standard



BAN

Connettore / supporto
per profili alluminio,



PRF-GPB

Guide for aluminium
profile, Rail for 8mm



PRT-TO

Corona girevole
Iglidur®, Con



PSG25

Ingranaggio dritto di
precisione, Inox 303

Prodotti correlati



BAB

Perno autobloccante a
sfere, Inox temprato



BABS

Perno autobloccante a
sfere inox 630, Inox
temprato



BABT

Perno autobloccante,
Inox temprato



BABreglabile

Perno autobloccante,
Regolabile