

# 12 and 24V DC power supplies



## ALIDR 30

Max current 1.5A or 2A

### Advantages

- Universal mains input
- Din rail mounting, DINTS35/7.5 or 15
- Protected against short circuits, overloads and over-voltage.
- Insulation class II
- LED supply indication
- Air-cooled
- 100% Burn-in

### Charateristics

- Output voltage can be varied by +/- 10%
- Max ripple on output +/- 1%

### Protections

- Max overload on output limited to 105/160%
- Output is short circuit protected
- Max overvoltage on output 115 to 135% of nominal output voltage

### Environment



- EMC: Conforms to EN55022 class B, EN61000-3-2,3, EN61000-6-2, EN61000-4-2,3,4,5,6,8,11, ENV50204, EN61204-3
- Max working temperature -20° to +50°C at 100% rated load (+60°C at 80% rated load)

### Connection

- Supply: 2 screw clamp terminals (0.2 to 2.5mm<sup>2</sup>)
- Output: 4 screw clamp terminals (0.2 to 2.5mm<sup>2</sup>)

### Dimensions/Material

- Enclosure: painted plastic
- Dimensions 93 x 78 x 56 (l x w x h)



Terminal n°	Connection	Terminal n°	Connection
1	AC/N	5,6	V-
2	AC/L	7	LED
3,4	V+	8	+VADJ

### DISCOUNTS

Qty.	1+	6+	10+
Disc. List	-7%	On request	

Part number	Supply voltage (V AC)	Output voltage (V DC)	Output current (A)	Weight (kg)	Price each 1 to 5
ALIDR30-12	85-264 / 120-370	12	2	0,27	46,80 €
ALIDR30-24	85-264 / 120-370	24	1,5	0,27	56,65 €


Dimensions in mm

## Altri prodotti...




PCF2

Supporto antivibrante cabina conico, Piastra a base ovale




EPRF

Dado flangiato per madrevite a passo lungo, Dado flangiato -fino a 4...



TBV

Tavola di posizionamento verticale manuale, Per corsa verticale - Co...



CYS

Anello di arresto interno DIN472, interno DIN 472



SSDB

Ingranaggio conico inox, 2:1




TCL-ECL

Piede massiccio per carichi pesanti, Vite a registro



M1

Coppia ruota e vite senza fine, Acciaio non temprato



BETASS

Copiglia beta, Beta



CHM30

Riduttore a ruota e vite senza fine, fino a



RPctcss

Ruota girevole a foro centrale, Inox -



HG5

Ingranaggio dritto acciaio, Acciaio



RLXAC8

Rullo folle, Acciaio

## Prodotti correlati



MAX26

Motoriduttore DC 12V e 24V DC, da 0,075 a 0,6Nm



BUH77

Motoriduttore DC 12V e 24V DC, da 0.1 a 2 Nm



MAX22

Motoriduttore DC 12V e 24V DC, da 0,07 a 0,2Nm



MAX22

Motoriduttore DC 12V e 24V DC, da 0,07 a 0,2Nm