




- Guide system for actuator
- Fitted with 4 smooth bronze bearings
- Slides protected by wiper joints
- Actuator coupling available on front face
- Supplied with fixing screw for actuator
- Maintenance free
- Working temperature: +5 to +80 °C
- Maximum speed: 1 m/s
- Maximum loads: See end of section
- Material:

Body + face plate:
anodised aluminium
Couplings + screws:
Zinc plated steel
Guide shafts:
Chromed steel

Excellent price/
Quality ratio

Accurate even over
long strokes



DISCOUNTS

Qty	1+	6+
Disc.	List	On request

Part number	Stroke	Ø Actuator	Ø Guide rod	Weight (kg)	Price each 1 to 5
UGH20-25	25	20	10	0,93	234,88 €
UGH20-50	50	20	10	0,96	236,00 €
UGH20-100	100	20	10	1,02	238,19 €
UGH20-160	160	20	10	1,09	240,81 €
UGH20-200	200	20	10	1,14	242,67 €
UGH20-250	250	20	10	1,20	244,87 €

Dimensions in mm