

- Ideal for moving bottles and metal cans at high speeds

- Smooth surface with no backlash
- Non knurled pin


- Materials:

Plates: low friction acetal

Pin: stainless steel 304

- Operating temp.: -40°C to +85°C (+70°C in humid environments)

- Length 3048mm (80 plates)





Advantages


- In most applications no lubrication is necessary

Associated products

- Drive sprocket **PT820**
- Idler sprocket **PR820**
- Idler **DBL820**



Direction of travel →



DISCOUNTS

Qty.	1+	5+	10+
Disc.	List	-5%	On request

Part number	Width K (mm)	Length (mm)	Breaking load (N)	Weight (kg/m)	Price each 1 to 4
CAP820-82	82,5	3048	3200	0,83	80,63 €
CAP820-114	114,3	3048	3200	1,03	102,69 €

Dimensions in mm

Altri prodotti...



HRV

Sistema di guida su binario a V Simple Select®, Binario con carrello



RDER55

Tenditore, a serraggio manuale inox



PR40

Piede fissabile con snodo - poliammide, Ø 50



PGM55

Maniglia a ponte inox, Inox



BAC105

Contenitore a becco, 8mm



PT882

Pignone di trazione, Serie 882



MC

Deceleratore, autocompensante - senza regolazione



EHD08-3

Riduttore coassiale, da 20 a 50 Nm



E30

Riduttore a rinvio angolare, da 1.50 a 9 Nm




BCM_MPBT

Spazzola cilindrica modulare, Filo poliestere PBT



MAX22

Motoriduttore DC 12V e 24V DC, da 0,07 a 0,2Nm



M0

Coppia ruota e vite senza fine, Plastica lavorata (delrin)

Prodotti correlati



PT820

Pignone di trazione, Serie 820 e 815



PR820

Ruota di rinvio, Serie 820 e 815



CAP815

Catena a tapparella dritta, Stretta serie 815



DBL820

Rotella per catena, Serie 820 e 815