

Male eyebolt **high resistance**



ADLMHR

High strenght alloy steel


- ISO thread
- Material:
High strenght alloy steel
grade 80 red painted

Stamping

- ØM, CE, WLL, manufacturer

Info

- The Breaking load is calculated
by multiplying the WLL by a safety
factor of 4"



DISCOUNTS

| | | | | |
|-------|------|------|------|------------|
| Qty | 1+ | 6+ | 20+ | 30+ |
| Disc. | List | -10% | -20% | On request |

| Part number | ØM | WLL (kg) | ØD1 | ØD2 | H | L | ØG | Weight (g) | Price each 1 to 5 |
|-------------|-----|----------|------|------|------|------|------|------------|-------------------|
| ADL-8M/HR | M8 | 800 | 45,0 | 25,0 | 46,0 | 13,0 | 25,0 | 110 | |
| ADL-10M/HR | M10 | 1000 | 45,0 | 24,5 | 46,5 | 17,0 | 25,0 | 110 | |
| ADL-12M/HR | M12 | 1600 | 54,0 | 30,0 | 55,0 | 20,0 | 30,0 | 180 | |
| ADL-14M/HR | M14 | 3000 | 63,0 | 34,5 | 63,0 | 21,0 | 35,0 | 280 | |
| ADL-16M/HR | M16 | 4000 | 63,0 | 35,0 | 64,0 | 27,0 | 35,0 | 300 | |
| ADL-18M/HR | M18 | 5000 | 72,0 | 40,0 | 72,0 | 30,0 | 40,0 | 450 | |
| ADL-20M/HR | M20 | 6000 | 72,3 | 39,7 | 71,8 | 30,2 | 40,3 | 475 | |
| ADL-22M/HR | M22 | 7000 | 90,3 | 49,8 | 91,1 | 34,3 | 50,0 | 880 | |
| ADL-24M/HR | M24 | 8000 | 90,0 | 50,0 | 90,4 | 38,0 | 50,2 | 905 | |

*Dimensions in mm



Female eyebolt **high resistance**

High strenght alloy steel

ADLHR


- ISO thread
- Material:
High strenght alloy steel grade 80
red painted

Stamping

- ØM, CE, WLL, manufacturer

Info

- The Breaking load is calculated by multiplying the WLL by a safety factor of 4"



DISCOUNTS

| | | | | |
|-------|------|------|------|------------|
| Qty | 1+ | 6+ | 20+ | 30+ |
| Disc. | List | -10% | -20% | On request |


| Part number | ØM | WLL (kg) | ØD1 | ØD2 | H | Weight (g) | Price each 1 to 5 |
|-------------|-----|----------|------|------|------|------------|-------------------|
| ADL-8F/HR | M8 | 800 | 45,5 | 24,9 | 46,0 | 100 | |
| ADL-10F/HR | M10 | 1000 | 45,4 | 24,7 | 46,5 | 100 | |
| ADL-12F/HR | M12 | 1600 | 54,2 | 29,9 | 54,4 | 165 | |
| ADL-14F/HR | M14 | 3000 | 63,3 | 34,9 | 64,0 | 250 | |
| ADL-16F/HR | M16 | 4000 | 63,2 | 35,0 | 63,3 | 245 | |
| ADL-18F/HR | M18 | 5000 | 72,1 | 39,7 | 73,1 | 380 | |
| ADL-20F/HR | M20 | 6000 | 72,0 | 39,9 | 71,7 | 365 | |
| ADL-22F/HR | M22 | 7000 | 90,4 | 49,9 | 91,8 | 760 | |
| ADL-24F/HR | M24 | 8000 | 90,2 | 50,0 | 92,0 | 740 | |

*Dimensions in mm

- **Lifting eye bolt**
- ISO thread
- **Material:**
Black stamped steel
Stainless steel 316

Mounting

- Chamfer the hole into which the bolt will screw or use washers to ensure correct seating.
- Before assembly, clean the threads
- Screw lifting eye in fully
- The load should be lifted in the direction of the thread, +/- 20° and the pulling force should be along the axial plane of the eye.
- The use of these lifting eyes at an angle greater than 45° is not permitted.
- When the load to be lifted is aluminium, avoid leaving the eyes screwed in to avoid possible corrosion.



Steel eye bolt

stainless steel



Stainless steel eye bolt

Info.

SWL: safe working load

The Safe Working Load is calculated by dividing the breaking strength by a factor of safety of 5.

DISCOUNTS

| | | | | |
|-------|------|------|------|------------|
| Qty | 1+ | 6+ | 20+ | 50+ |
| Disc. | List | -10% | -20% | On request |


| Part number | Ød | H | ØD1 | ØD2 | ØG | E | ØS | SWL (kg) | SWL at 45° (kg) | Weight (kg) | Price each 1 to 5 |
|---------------------------------|-----|-----|-----|-----|-----|----|----|----------|-----------------|-------------|-------------------|
| Steel eye bolt | | | | | | | | | | | |
| ADL-6F | M6 | 36 | 36 | 20 | 22 | 9 | 9 | 90 | 60 | 0,060 | ✓ 1,93 € |
| ADL-8F | M8 | 36 | 36 | 20 | 21 | 11 | 9 | 140 | 95 | 0,060 | ✓ 1,96 € |
| ADL-10F | M10 | 45 | 45 | 25 | 26 | 10 | 10 | 230 | 170 | 0,100 | ✓ 2,31 € |
| ADL-12F | M12 | 52 | 55 | 29 | 31 | 11 | 12 | 340 | 240 | 0,160 | ✓ 3,14 € |
| ADL-16F | M16 | 62 | 63 | 34 | 34 | 15 | 14 | 700 | 500 | 0,240 | ✓ 4,40 € |
| ADL-20F | M20 | 71 | 72 | 39 | 40 | 17 | 16 | 1200 | 830 | 0,360 | ✓ 6,89 € |
| ADL-24F | M24 | 89 | 90 | 48 | 49 | 22 | 21 | 1800 | 1270 | 0,715 | - 12,21 € |
| ADL-30F | M30 | 109 | 108 | 60 | 65 | 25 | 24 | 3200 | 2300 | 1,400 | - 23,86 € |
| ADL-36F | M36 | 137 | 127 | 69 | 81 | 38 | 31 | 4600 | 3300 | 2,300 | - 41,40 € |
| ADL-42F | M42 | 147 | 144 | 80 | 85 | 35 | 32 | 6300 | 4500 | 3,500 | - 81,17 € |
| ADL-48F | M48 | 185 | 170 | 88 | 102 | 45 | 41 | 8600 | 6100 | 5,670 | - 130,90 € |
| Stainless steel eye bolt | | | | | | | | | | | |
| ADL-6F/SS | M6 | - | 35 | 19 | 20 | 9 | 9 | 180 | - | 0,055 | ✓ 7,01 € |
| ADL-8F/SS | M8 | - | 36 | 19 | 20 | 10 | 8 | 300 | - | 0,050 | ✓ 7,90 € |
| ADL-10F/SS | M10 | - | 45 | 24 | 24 | 11 | 9 | 500 | - | 0,090 | ✓ 13,10 € |
| ADL-12F/SS | M12 | - | 53 | 29 | 29 | 13 | 12 | 800 | - | 0,155 | ✓ 18,32 € |
| ADL-14F/SS | M14 | - | 54 | 30 | 30 | 11 | 12 | 1100 | - | 0,165 | - 20,93 € |
| ADL-16F/SS | M16 | - | 63 | 34 | 35 | 15 | 14 | 1500 | - | 0,250 | ✓ 24,09 € |
| ADL-20F/SS | M20 | - | 72 | 40 | 40 | 15 | 16 | 2400 | - | 0,360 | - 44,33 € |
| ADL-24F/SS | M24 | - | 90 | 50 | 50 | 20 | 20 | 3600 | - | 0,720 | - 79,17 € |

*Depending on availability - Dimensions in mm

- **Lifting eye bolt**
- ISO thread
- Material:
Black stamped steel
Stainless steel 316

Mounting

- Chamfer the hole into which the bolt will screw or use washers to ensure correct seating.
- Before assembly, clean the threads
- Screw lifting eye in fully
- The load should be lifted in the direction of the thread, +/- 20° and the pulling force should be along the axial plane of the eye.
- The use of these lifting eyes at an angle greater than 45° is not permitted.
- When the load to be lifted is aluminium, avoid leaving the eyes screwed in to avoid possible corrosion.



Steel eye bolt



Stainless steel eye bolt

Info.

SWL: safe working load
The Safe Working Load is calculated by dividing the breaking Strength by a factor of safety of 5.

DISCOUNTS

| | | | | |
|-------|-----------|------|------------|-----|
| Qty | 1+ | 6+ | 20+ | 50+ |
| Disc. | List -10% | -20% | On request | |

| Part number | Ød | L | H | ØD1 | ØD2 | ØG | E | ØS | SWL (kg) | SWL at 45° (kg) | Weight (kg) | Price each 1 to 5 |
|---------------------------------|-----|----|-----|-----|-----|-----|----|----|----------|-----------------|-------------|-------------------|
| Steel eye bolt | | | | | | | | | | | | |
| ADL-6M | M6 | 13 | 36 | 36 | 20 | 20 | 6 | 8 | 90 | 60 | 0,060 | ✓ 1,96 € |
| ADL-8M | M8 | 13 | 38 | 36 | 20 | 21 | 7 | 9 | 140 | 95 | 0,060 | ✓ 2,00 € |
| ADL-10M | M10 | 16 | 46 | 45 | 24 | 26 | 9 | 10 | 230 | 170 | 0,110 | ✓ 2,43 € |
| ADL-12M | M12 | 19 | 56 | 55 | 29 | 30 | 12 | 11 | 340 | 240 | 0,170 | ✓ 2,96 € |
| ADL-16M | M16 | 28 | 65 | 64 | 36 | 35 | 12 | 14 | 700 | 500 | 0,290 | ✓ 4,62 € |
| ADL-20M | M20 | 30 | 74 | 72 | 40 | 40 | 14 | 17 | 1200 | 830 | 0,450 | ✓ 6,89 € |
| ADL-24M | M24 | 36 | 92 | 89 | 49 | 51 | 18 | 21 | 1800 | 1270 | 0,880 | ✓ 11,71 € |
| ADL-30M | M30 | 43 | 111 | 108 | 60 | 65 | 23 | 25 | 3200 | 2300 | 1,640 | ✓ 22,24 € |
| ADL-36M | M36 | 54 | 131 | 126 | 68 | 80 | 24 | 29 | 4600 | 3300 | 2,710 | - 38,68 € |
| ADL-42M | M42 | 61 | 153 | 148 | 79 | 90 | 33 | 35 | 6300 | 4500 | 4,250 | - 73,24 € |
| ADL-48M | M48 | 68 | 168 | 166 | 90 | 100 | 35 | 38 | 8600 | 6100 | 6,200 | - 126,91 € |
| Stainless steel eye bolt | | | | | | | | | | | | |
| ADL-6M/SS | M6 | 13 | - | 35 | 20 | 20 | 7 | 8 | 180 | - | 0,050 | ✓ 7,46 € |
| ADL-8M/SS | M8 | 13 | - | 36 | 20 | 20 | 6 | 8 | 300 | - | 0,060 | ✓ 7,97 € |
| ADL-10M/SS | M10 | 17 | - | 45 | 25 | 25 | 8 | 10 | 500 | - | 0,115 | ✓ 13,46 € |
| ADL-12M/SS | M12 | 20 | - | 54 | 30 | 30 | 10 | 12 | 800 | - | 0,190 | ✓ 18,70 € |
| ADL-14M/SS | M14 | 20 | - | 54 | 30 | 30 | 10 | 12 | 1100 | - | 0,190 | ✓ 21,49 € |
| ADL-16M/SS | M16 | 27 | - | 63 | 35 | 35 | 12 | 14 | 1500 | - | 0,280 | ✓ 27,19 € |
| ADL-20M/SS | M20 | 30 | - | 72 | 40 | 40 | 14 | 16 | 2400 | - | 0,450 | - 45,38 € |
| ADL-24M/SS | M24 | 35 | - | 90 | 50 | 50 | 17 | 22 | 3600 | - | 0,900 | - 87,60 € |

* Depending on availability - Dimensions in mm


Altri prodotti...



PTA100
Piede snodato con base stampata Ø100, 15000N



FTSN
Albero supportato per guida lineare, Albero acciaio / supporto allu...



RPP3
Cinghia di trasmissione RPP, RPP3



BABS303
Perno autobloccante inox 303, Inox 303



RFVbr
Riduttore inox a ruota e vite senza fine, Braccio di reazione



HTD5M_15
Puleggia dentata di trasmissione tipo HTD, HTD5 Acciaio



PGMSS
Maniglia a ponte inox, Inox



RBNpl
Ruota fissa con piastra, Acciaio - caucciù



WFRM
Dado trapezoidale, Polimero (Iglidur®) - 1



BC3
Panamech, Multi-Beam inox, Inox - con



KBS_UU
Manicotto chiuso a sfere inox di



PENV
Maniglia da incasso, Ad avvitare

Prodotti correlati



CRLHR
Anello di sollevamento,



ADL_F
Anello di sollevamento, Acciaio



ADL_F
Anello di sollevamento, Inox



VRM
Anello di sollevamento, Orientabile femmina