
Slim plate chain

CAP820

Range 820

- ***Ideal for moving bottles and metal cans at high speeds***
- *Smooth surface with no backlash*
- *Non knurled pin*
- *Materials:*
  Plates: low friction acetal
  Pin: stainless steel 304
- *Operating temp.: -40°C to +85°C (+70°C in humid environments)*
- *Length 3048mm (80 plates)*




Advantages

- *In most applications no lubrication is necessary*

Associated products

- *Drive sprocket* **PT820**
- *Idler sprocket* **PR820**
- *Idler* **DBL820**



DISCOUNTS

Qty.	1+	5+	10+
Disc.	List	-5%	On request

Part number	Width K (mm)	Length (mm)	Breaking load (N)	Weight (kg/m)	Price each 1 to 4
CAP820-82	82,5	3048	3200	0,83	80,63 €
CAP820-114	114,3	3048	3200	1,03	102,69 €

Dimensions in mm

Altri prodotti...



Piedino antivibrante parabolico, Acciaio



Flanged nut for ball screw, For VAB ballscrew



Golfare di sollevamento, alta resistenza



Deceleratore, Flangia rettangolare



Riduttore a ruota e vite senza fine, fino a 8.80 Nm



Vite senza fine di precisione, Acciaio



Box kit di spine cilindriche DIN6325, Box kit - standard DIN 6325



Ingranaggio conico in plastica, 2:1



Economic mini-table with trapezoidal



Fascette di serraggio, Valigetta di fascette



Cerniere e giunti, Fulcro per porta



Accessori di collegamento, Piastra

Prodotti correlati



Pignone di trazione, Serie 820 e 815



Ruota di rinvio, Serie 820 e 815



Catena a tapparella dritta, Stretta serie 815



Rotella per catena, Serie 820 e 815