

# Side flexing slim plate chain



## CAP880T

## Range 880 TAB

- **Bending radius allows chain to follow a curved path**


- **Materials:**

Plates: low friction acetal

Pin: stainless steel 304

- Operating temp.: -40°C to +85°C  
(+70°C in humid environments)

- Length 3048mm (80 plates)



### Advantages

- Special shape prevents products being carried moving or falling whilst on curves

### Associated products


- Drive sprocket **PT880**

- Idler sprocket **PR880**


- Idler **DBL880**

- Straight track **GRD880T**


- Curved track **GCB880T**



A  $\left\{ \begin{array}{l} \text{Straight} - 46 \\ \text{Curved} - 44,2 \end{array} \right.$



Typical application



### DISCOUNTS

Qty.	1+	5+	10+
Disc. List	-5%	On request	

Part number	Width K (mm)	Length (mm)	Bend radius RM (mm)	Breaking load (N)	Weight (kg/m)	Price each 1 to 4
CAP880T-82	82,5	3048	457	5200	1,04	106,93 €
CAP880T-114	114,3	3048	532	5200	1,21	122,84 €

Dimensions in mm

## Altri prodotti...



AT10courroie

Cinghia di posizionamento AT, AT10 Poliuretano armatura in acciaio



CAP882

Catena a tapparella, Larga serie 882



BLHT60

Rinvio angolare a T, da 26 a 70 Nm



BCM\_TP

Spazzola cilindrica modulare, Filo in tampico



OP7

Indicatore di posizione digitale (N. di giri), 5 cifre




PRF\_CHA D

Cerniera ad avvitare, Scardinabile



CHAL3

Cerniera piana, Acciaio



T2

Cinghia di posizionamento T, T2.5 Poliuretano armatura in acciaio



WJUM20

Pattino Drylin® W, Pattino



GDR880

Guida dritta, Serie 880 e 881



BSM\_LOK

Pressore a molla con esagono incassato, LONG-LOK - corpo e



DOG316

Motoriduttore DC 12V e 24V DC, da 1.5 a 2 Nm

## Prodotti correlati



PR880

Ruota di rinvio, Serie 880



PT880

Pignone di trazione, Serie 880



CAP881

Catena a tapparella, Stretta serie 881



GDR880

Guida dritta, Serie 880 e 881