Flanged polymer bush

AFM For food and pharmaceutical industries

- ***Material*: iglidur® A200**
- *Approved by the Food and Drug Administration (FDA)*
- *High resistance*
- *High abrasion resistance*
- *Suitable for slow oscillating, rotary or linear movements*
- *Working temp. -40°C to +80°C (short periods +170°C)*
- *For mechanical performance characteristics, please see ASM bush*
- ***Not sold individually, please contact us for details***

Maintenance free



DISCOUNTS


Qty.	1+	10+	25+	50+	100+	200+	500+
Disc.	List	-10%	-25%	-45%	-60%	-65%	On request

Part number	Ød1	Ød2	Ød3 ^{js13}	b1 ^{h13}	b2 $^{-0.14}$	f	Stock*	Price each 1 to 9
AFM0103-02	1,0 $^{+0,020\ +0,080}$	3	5	2	1,0	0,5	✔	2,80 €
AFM0104-02	1,5 $^{+0,020\ +0,080}$	4	6	2	1,0	0,5	-	2,80 €
AFM0205-03	2,0 $^{+0,020\ +0,080}$	5	8	3	1,5	0,5	✔	3,94 €
AFM0206-03	2,5 $^{+0,020\ +0,080}$	6	9	3	1,5	0,5	-	2,86 €
AFM0306-04	3,0 $^{+0,020\ +0,080}$	6	9	4	1,5	0,5	✔	3,94 €
AFM0408-04	4,0 $^{+0,030\ +0,105}$	8	12	4	2,0	0,5	✔	4,03 €
AFM0408-06	4,0 $^{+0,030\ +0,105}$	8	12	6	2,0	0,5	✔	4,03 €
AFM0509-05	5,0 $^{+0,030\ +0,105}$	9	13	5	2,0	0,5	-	3,07 €
AFM0509-06	5,0 $^{+0,030\ +0,105}$	9	13	6	2,0	0,5	-	3,07 €
AFM0509-08	5,0 $^{+0,030\ +0,105}$	9	13	8	2,0	0,5	✔	4,15 €
AFM0610-04	6,0 $^{+0,030\ +0,105}$	10	14	4	2,0	0,5	✔	4,03 €
AFM0610-06	6,0 $^{+0,030\ +0,105}$	10	14	6	2,0	0,5	-	4,15 €
AFM0610-10	6,0 $^{+0,030\ +0,105}$	10	14	10	2,0	0,5	-	4,15 €
AFM0612-06	6,0 $^{+0,030\ +0,105}$	12	14	6	3,0	0,5	-	3,12 €
AFM0612-10	6,0 $^{+0,030\ +0,105}$	12	14	10	3,0	0,5	-	3,12 €
AFM0711-08	7,0 $^{+0,040\ +0,130}$	11	15	8	2,0	0,5	-	3,28 €
AFM0811-08	8,0 $^{+0,040\ +0,130}$	11	13	8	2,0	0,5	✔	4,35 €
AFM0812-06	8,0 $^{+0,040\ +0,130}$	12	16	6	2,0	0,5	✔	4,26 €
AFM0812-08	8,0 $^{+0,040\ +0,130}$	12	16	8	2,0	0,5	✔	2,58 €
AFM0812-12	8,0 $^{+0,040\ +0,130}$	12	16	12	2,0	0,5	✔	3,49 €
AFM0814-06	8,0 $^{+0,040\ +0,130}$	14	18	6	3,0	0,5	-	3,35 €
AFM0814-10	8,0 $^{+0,040\ +0,130}$	14	18	10	3,0	0,5	-	3,35 €
AFM0914-06	9,0 $^{+0,040\ +0,130}$	14	19	6	3,0	0,5	-	3,28 €
AFM0914-10	9,0 $^{+0,040\ +0,130}$	14	19	10	3,0	0,5	-	3,35 €
AFM0914-14	9,0 $^{+0,040\ +0,130}$	14	19	14	3,0	0,5	-	3,45 €
AFM10162010	10,0 $^{+0,040\ +0,130}$	16	20	10	3,0	0,5	✔	3,53 €
AFM1016-08	10,0 $^{+0,040\ +0,130}$	16	22	8	3,0	0,5	✔	4,52 €
AFM1016-10	10,0 $^{+0,040\ +0,130}$	16	22	10	3,0	0,5	-	3,53 €
AFM1016-16	10,0 $^{+0,040\ +0,130}$	16	22	16	3,0	0,5	✔	4,68 €
AFM1218-08	12,0 $^{+0,050\ +0,160}$	18	24	8	3,0	0,8	✔	3,53 €
AFM1218-10	12,0 $^{+0,050\ +0,160}$	18	22	10	3,0	0,8	-	3,53 €
AFM1218-12	12,0 $^{+0,050\ +0,160}$	18	24	12	3,0	0,8	✔	2,96 €
AFM1218-15	12,0 $^{+0,050\ +0,160}$	18	22	15	3,0	0,8	✔	4,72 €

**Depending on availability - Dimensions in mm*

Assembly

- *Recommended assembly tolerances: shaft h9 housing bore-size H7*
- *Treated shaft 50 HRc*
- *Surface finish 1.5-3 µm*



DISCOUNTS

Qty.	1+	10+	25+	50+	100+	200+	500+
Disc.	List	-10%	-25%	-45%	-60%	-65%	On request

Part number	Ød1	Ød2	Ød3 d13	b1 h13	b2 h,14	f	Stock*	Price each 1 to 9
AFM1218-20	12 +0,050 +0,160	18	22	20	3,0	0,8	✔	4,84 €
AFM1420-10	14 +0,050 +0,160	20	25	10	3,0	0,8	-	3,72 €
AFM1420-15	14 +0,050 +0,160	20	25	15	3,0	0,8	✔	4,89 €
AFM1420-20	14 +0,050 +0,160	20	25	20	3,0	0,8	✔	5,00 €
AFM1521-10	15 +0,050 +0,160	21	27	10	3,0	0,8	-	3,76 €
AFM1521-15	15 +0,050 +0,160	21	27	15	3,0	0,8	✔	4,95 €
AFM1521-20	15 +0,050 +0,160	21	27	20	3,0	0,8	✔	5,00 €
AFM1521-25	15 +0,050 +0,160	21	27	25	3,0	0,8	-	4,03 €
AFM1622-12	16 +0,050 +0,160	22	28	12	3,0	0,8	✔	3,76 €
AFM1622-15	16 +0,050 +0,160	22	28	15	3,0	0,8	✔	4,89 €
AFM1622-20	16 +0,050 +0,160	22	28	20	3,0	0,8	-	3,99 €
AFM1622-25	16 +0,050 +0,160	22	28	25	3,0	0,8	✔	5,15 €
AFM1824-12	18 +0,050 +0,160	24	30	12	3,0	0,8	✔	4,89 €
AFM1824-18	18 +0,050 +0,160	24	30	18	3,0	0,8	-	3,99 €
AFM1824-20	18 +0,050 +0,160	24	30	20	3,0	0,8	-	3,99 €
AFM1824-30	18 +0,050 +0,160	24	30	30	3,0	0,8	✔	5,49 €
AFM2026-15	20 +0,065 +0,195	26	32	15	3,0	0,8	✔	5,00 €
AFM2026-20	20 +0,065 +0,195	26	32	20	3,0	0,8	✔	5,33 €
AFM2026-30	20 +0,065 +0,195	26	32	30	3,0	0,8	✔	5,53 €
AFM2228-15	22 +0,065 +0,195	28	34	15	3,0	0,8	-	5,26 €
AFM2228-20	22 +0,065 +0,195	28	34	20	3,0	0,8	-	4,41 €
AFM2228-30	22 +0,065 +0,195	28	34	30	3,0	0,8	-	5,85 €
AFM2430-15	24 +0,065 +0,195	30	36	15	3,0	0,8	-	4,19 €
AFM2430-20	24 +0,065 +0,195	30	36	20	3,0	0,8	-	4,41 €
AFM2430-30	24 +0,065 +0,195	30	36	30	3,0	0,8	-	5,00 €
AFM2532-20	25 +0,065 +0,195	32	38	20	4,0	0,8	✔	5,85 €
AFM2532-30	25 +0,065 +0,195	32	38	30	4,0	0,8	-	5,49 €
AFM2532-40	25 +0,065 +0,195	32	38	40	4,0	0,8	✔	6,97 €
AFM2734-20	27 +0,065 +0,195	34	40	20	4,0	0,8	-	5,00 €
AFM2734-30	27 +0,065 +0,195	34	40	30	4,0	0,8	-	5,59 €
AFM2734-40	27 +0,065 +0,195	34	40	40	4,0	0,8	-	6,08 €
AFM2836-20	28 +0,065 +0,195	36	42	20	4,0	0,8	-	5,22 €
AFM2836-30	28 +0,065 +0,195	36	42	30	4,0	0,8	-	5,89 €
AFM2836-40	28 +0,065 +0,195	36	42	40	4,0	0,8	-	6,60 €
AFM3038-20	30 +0,065 +0,195	38	44	20	4,0	0,8	✔	6,28 €
AFM3038-30	30 +0,065 +0,195	38	44	30	4,0	0,8	✔	7,11 €
AFM3038-40	30 +0,065 +0,195	38	44	40	4,0	0,8	✔	7,84 €
AFM3240-20	32 +0,080 +0,240	40	46	20	4,0	1,2	-	5,26 €
AFM3240-30	32 +0,080 +0,240	40	46	30	4,0	1,2	-	6,23 €
AFM3240-40	32 +0,080 +0,240	40	46	40	4,0	1,2	-	7,11 €

**Depending on availability - Dimensions in mm*


Altri prodotti...


SCE

Serracavo, Acciaio


PSG1

Ingranaggio dritto di precisione, Acciaio 35NCD6 pretrattato


PCF4

Supporto antivibrante cabina conico, Piastra a base quadrata


PDM_PDV

Detectable plastic palm grip, blue thermoplastic


M1

Vite senza fine , Acciaio temprato


PLM-20SC

Magnete cilindrico, Magnete cilindrico



TBV

Tavola di posizionamento verticale manuale, 20kg


BAG

Anello di bloccaggio in acciaio, Acciaio


PPCss

Piastrina con anello, Inox


V3RA_PT

Volantino a tre razze, Poliammide


WJUM20

Pattino Drylin® W, Pattino


RURp

Rotella girevole con piastra, Poliuretano - Mozzo alluminio (Ultra s...

Prodotti correlati


ASM

Cuscinetto cilindrico , Polimero alimentare


JFM

Cuscinetto a collare , Polimero universale