

Flanged polymer bush



AFM For food and pharmaceutical industries

- Material: iglidur® A200
- Approved by the Food and Drug Administration (FDA)
- High resistance
- High abrasion resistance
- Suitable for slow oscillating, rotary or linear movements
- Working temp. -40°C to +80°C (short periods +170°C)
- For mechanical performance characteristics, please see ASM bush
- Not sold individually, please contact us for details

Maintenance free



DISCOUNTS


Qty.	1+	10+	25+	50+	100+200+	500+
Disc.	List	-10%	-25%	-45%	-60%	-65% On request

Part number	Ød1	Ød2	Ød3 ^{±0.13}	b1 ^{±0.13}	b2 ^{±0.14}	f	Stock*	Price each 1 to 9
AFM0103-02	1,0 ^{+0.020 +0.080}	3	5	2	1,0	0,5	✓	2.80 €
AFM0104-02	1,5 ^{+0.020 +0.080}	4	6	2	1,0	0,5	-	2.80 €
AFM0205-03	2,0 ^{+0.020 +0.080}	5	8	3	1,5	0,5	✓	3.94 €
AFM0206-03	2,5 ^{+0.020 +0.080}	6	9	3	1,5	0,5	✓	2.86 €
AFM0306-04	3,0 ^{+0.020 +0.080}	6	9	4	1,5	0,5	✓	3.94 €
AFM0408-04	4,0 ^{+0.030 +0.105}	8	12	4	2,0	0,5	✓	4.03 €
AFM0408-06	4,0 ^{+0.030 +0.105}	8	12	6	2,0	0,5	✓	4.03 €
AFM0509-05	5,0 ^{+0.030 +0.105}	9	13	5	2,0	0,5	-	3.07 €
AFM0509-06	5,0 ^{+0.030 +0.105}	9	13	6	2,0	0,5	-	3.07 €
AFM0509-08	5,0 ^{+0.030 +0.105}	9	13	8	2,0	0,5	✓	4.15 €
AFM0610-04	6,0 ^{+0.030 +0.105}	10	14	4	2,0	0,5	✓	4.03 €
AFM0610-06	6,0 ^{+0.030 +0.105}	10	14	6	2,0	0,5	-	4.15 €
AFM0610-10	6,0 ^{+0.030 +0.105}	10	14	10	2,0	0,5	-	4.15 €
AFM0612-06	6,0 ^{+0.030 +0.105}	12	14	6	3,0	0,5	-	3.12 €
AFM0612-10	6,0 ^{+0.030 +0.105}	12	14	10	3,0	0,5	-	3.12 €
AFM0711-08	7,0 ^{+0.040 +0.130}	11	15	8	2,0	0,5	-	3.28 €
AFM0811-08	8,0 ^{+0.040 +0.130}	11	13	8	2,0	0,5	✓	4.35 €
AFM0812-06	8,0 ^{+0.040 +0.130}	12	16	6	2,0	0,5	✓	4.26 €
AFM0812-08	8,0 ^{+0.040 +0.130}	12	16	8	2,0	0,5	✓	2.58 €
AFM0812-12	8,0 ^{+0.040 +0.130}	12	16	12	2,0	0,5	✓	3.49 €
AFM0814-06	8,0 ^{+0.040 +0.130}	14	18	6	3,0	0,5	-	3.35 €
AFM0814-10	8,0 ^{+0.040 +0.130}	14	18	10	3,0	0,5	-	3.35 €
AFM0914-06	9,0 ^{+0.040 +0.130}	14	19	6	3,0	0,5	-	3.28 €
AFM0914-10	9,0 ^{+0.040 +0.130}	14	19	10	3,0	0,5	-	3.35 €
AFM0914-14	9,0 ^{+0.040 +0.130}	14	19	14	3,0	0,5	-	3.45 €
AFM10162010	10,0 ^{+0.040 +0.130}	16	20	10	3,0	0,5	✓	3.53 €
AFM1016-08	10,0 ^{+0.040 +0.130}	16	22	8	3,0	0,5	✓	4.52 €
AFM1016-10	10,0 ^{+0.040 +0.130}	16	22	10	3,0	0,5	-	3.53 €
AFM1016-16	10,0 ^{+0.040 +0.130}	16	22	16	3,0	0,5	✓	4.68 €
AFM1218-08	12,0 ^{+0.050 +0.160}	18	24	8	3,0	0,8	✓	3.53 €
AFM1218-10	12,0 ^{+0.050 +0.160}	18	22	10	3,0	0,8	-	3.53 €
AFM1218-12	12,0 ^{+0.050 +0.160}	18	24	12	3,0	0,8	✓	2.96 €
AFM1218-15	12,0 ^{+0.050 +0.160}	18	22	15	3,0	0,8	✓	4.72 €

*Depending on availability - Dimensions in mm

Assembly

- Recommended assembly tolerances:
shaft h9
housing bore-size H7
- Treated shaft 50 HRC
- Surface finish 1.5-3 μm

**DISCOUNTS**

Qty.	1+	10+	25+	50+	100+	200+	500+
Disc.	List	-10%	-25%	-45%	-60%	-65%	On request

Part number	Ød1	Ød2	Ød3 ¹¹³	b1 ¹¹³	b2 ¹¹⁴	f	Stock*	Price each 1 to 9
AFM1218-20	12 ^{+0,050 +0,160}	18	22	20	3,0	0,8	✓	4,84 €
AFM1420-10	14 ^{+0,050 +0,160}	20	25	10	3,0	0,8	-	3,72 €
AFM1420-15	14 ^{+0,050 +0,160}	20	25	15	3,0	0,8	✓	4,89 €
AFM1420-20	14 ^{+0,050 +0,160}	20	25	20	3,0	0,8	✓	5,00 €
AFM1521-10	15 ^{+0,050 +0,160}	21	27	10	3,0	0,8	-	3,76 €
AFM1521-15	15 ^{+0,050 +0,160}	21	27	15	3,0	0,8	✓	4,95 €
AFM1521-20	15 ^{+0,050 +0,160}	21	27	20	3,0	0,8	✓	5,00 €
AFM1521-25	15 ^{+0,050 +0,160}	21	27	25	3,0	0,8	-	4,03 €
AFM1622-12	16 ^{+0,050 +0,160}	22	28	12	3,0	0,8	✓	3,76 €
AFM1622-15	16 ^{+0,050 +0,160}	22	28	15	3,0	0,8	✓	4,89 €
AFM1622-20	16 ^{+0,050 +0,160}	22	28	20	3,0	0,8	-	3,99 €
AFM1622-25	16 ^{+0,050 +0,160}	22	28	25	3,0	0,8	✓	5,15 €
AFM1824-12	18 ^{+0,050 +0,160}	24	30	12	3,0	0,8	✓	4,89 €
AFM1824-18	18 ^{+0,050 +0,160}	24	30	18	3,0	0,8	-	3,99 €
AFM1824-20	18 ^{+0,050 +0,160}	24	30	20	3,0	0,8	-	3,99 €
AFM1824-30	18 ^{+0,050 +0,160}	24	30	30	3,0	0,8	✓	5,49 €
AFM2026-15	20 ^{+0,065 +0,195}	26	32	15	3,0	0,8	✓	5,00 €
AFM2026-20	20 ^{+0,065 +0,195}	26	32	20	3,0	0,8	✓	5,33 €
AFM2026-30	20 ^{+0,065 +0,195}	26	32	30	3,0	0,8	✓	5,53 €
AFM2228-15	22 ^{+0,065 +0,195}	28	34	15	3,0	0,8	-	5,26 €
AFM2228-20	22 ^{+0,065 +0,195}	28	34	20	3,0	0,8	-	4,41 €
AFM2228-30	22 ^{+0,065 +0,195}	28	34	30	3,0	0,8	-	5,85 €
AFM2430-15	24 ^{+0,065 +0,195}	30	36	15	3,0	0,8	-	4,41 €
AFM2430-20	24 ^{+0,065 +0,195}	30	36	20	3,0	0,8	-	4,41 €
AFM2430-30	24 ^{+0,065 +0,195}	30	36	30	3,0	0,8	-	5,00 €
AFM2532-20	25 ^{+0,065 +0,195}	32	38	20	4,0	0,8	✓	5,85 €
AFM2532-30	25 ^{+0,065 +0,195}	32	38	30	4,0	0,8	-	5,49 €
AFM2532-40	25 ^{+0,065 +0,195}	32	38	40	4,0	0,8	✓	6,97 €
AFM2734-20	27 ^{+0,065 +0,195}	34	40	20	4,0	0,8	-	5,00 €
AFM2734-30	27 ^{+0,065 +0,195}	34	40	30	4,0	0,8	-	5,59 €
AFM2734-40	27 ^{+0,065 +0,195}	34	40	40	4,0	0,8	-	6,08 €
AFM2836-20	28 ^{+0,065 +0,195}	36	42	20	4,0	0,8	-	5,22 €
AFM2836-30	28 ^{+0,065 +0,195}	36	42	30	4,0	0,8	-	5,89 €
AFM2836-40	28 ^{+0,065 +0,195}	36	42	40	4,0	0,8	-	6,60 €
AFM3038-20	30 ^{+0,065 +0,195}	38	44	20	4,0	0,8	✓	6,28 €
AFM3038-30	30 ^{+0,065 +0,195}	38	44	30	4,0	0,8	✓	7,11 €
AFM3038-40	30 ^{+0,065 +0,195}	38	44	40	4,0	0,8	✓	7,84 €
AFM3240-20	32 ^{+0,080 +0,240}	40	46	20	4,0	1,2	-	5,26 €
AFM3240-30	32 ^{+0,080 +0,240}	40	46	30	4,0	1,2	-	6,23 €
AFM3240-40	32 ^{+0,080 +0,240}	40	46	40	4,0	1,2	-	7,11 €

*Depending on availability - Dimensions in mm

Altri prodotti...



HLUT
Volantino con razze e impugnatura girevole, Alluminio



MAX22
Motoriduttore DC 12V e 24V DC, da 0,07 a 0,2Nm



DFG
Ventosa, silicone



GG1
Ingranaggio dritto rettificato, Acciaio trattato



MRS
Cremagliera sezione metrica, Inox




METC
Cuscinetto a collare, Bronzo autolubrificante



KSTM
Supporto ritto con cuscinetto Igubal®, Polimero



LRX
Guida lineare a rulli, Carello - da 9410 N a 101000 N



PRL
Profilo supporto per catena, Profilo ad L ad incastro



PSG35
Ingranaggio dritto di precisione, Inox 316



SUP
Calettatore di bloccaggio autocentrante acciaio,




KB_WW
Manicotto chiuso a sfere di precisione, Economica

Prodotti correlati



ASM
Cuscinetto cilindrico, Polimero alimentare



JFM
Cuscinetto a collare, Polimero universale