

24V DC power supply



ALIDRP 240

Max current 10A

Advantages

- Universal Mains supply.
PF>0.98@115Vac, PF>0.95@230Vac
- Protected against short circuits, overloads and over-voltage
- Switching frequency : 100KHz
- UL508 listed
- Din rail mounting, DINTS35/7.5 or 15.
- LED supply indication
- Air-cooled
- 100% Burn-in

Charateristics

- Output voltage can be varied from 24 to 48V dc
- Max ripple on output +/- 1%

Protections

- Max overload on output limited to 105 to150%
- Output is short circuit protected
- Max overvoltage on output 30 to 36 V dc

Environment


- EMC: Conforms to EN55022 class B, EN61000-3-2,3, EN61000-6-2, EN61000-4-2,3,4,5,6,8,11, ENV50204, EN61204-3
- Personnel safety: Conforms to UL508, UL60950-1, TUV60950-1
- Max working temperature -10° to +50°C @100% load, +70°C @60% load (natural convection)

Connection

- Supply: 3 screw clamp terminals DIN
- Output: 4 screw clamp terminals DIN

Dimensions/Material

- Enclosure: painted plastic
- Dimensions 125.5 x 125.2 x 100 (l x w x h)



TERMINAL ASSIGNMENT (TB1)

Contact n°	Affectation
1	FG Ⓢ
2	AC/N
3	AC/L

TERMINAL ASSIGNMENT (TB2)

Terminal n°	Connection
1,2	DC OUTPUT +V
3,4	DC OUTPUT -V

DISCOUNTS

Qty.	1+	6+	10+
Disc. List	-7%	On request	

Part number	Supply voltage (V AC)	Output voltage (V DC)	Output current (A)	Weight (kg)	Price each 1 to 5
ALIDRP240-24	85-264 / 120-370	24	10	1,2	206,95 €

Dimensions in mm

Altri prodotti...



TIFss

Tirante tutto filetto -
DIN976A, Inox




CHAE4080PA

Cerniera ad avvitare
estetica simmetrica,
Poliammide



HK

Accessorio di
serraggio manuale,
Serraggio manuale
LWL




B

Ingranaggio conico -
Acciaio 60C40, 1:1



DILC

Indexing plunger with
cam, with cam



EPRF

Dado flangiato per
madrevite a passo
lungo, Dado flangiato
-fino a 4...



GE_C

Snodo sferico, Cromo
duro/PTFE



R203

Molla per stampi
ISO10243, Leggero



RLR

Tenditore per catene
Roll-Ring®, Roll-
Ring® Self-adjusting



PLA

Magnete piatto,
Magnete piatto



PW_PWG2

Vite senza fine di
precisione, Acciaio



PAMF120

Articulated fixable
foot, pressed bolt-
down base Ø 120, Ø
120

Prodotti correlati



DOG319

Motoriduttore DC 12V
e 24V DC, da 4 a 9
Nm



DOG258

Motoriduttore DC 12V
e 24V DC, da 12 a 15
Nm