


Module 8,0

C45 Steel

- Economical gear range
- Pressure angle 20°
- Material:
C45 steel UNI7845

Info.

- * Pre-bore information is given as a guide only and may vary between batches
- Gear should be finished to suit the application
- **We are unable to modify these gears**



economic series

DISCOUNTS

Qty	1+	4+	10+
Disc.	List	-5%	On request

Part number	Z Teeth	ØP PCD	ØD External	ØM Hub	ØA Pre-bore	Weight (kg)	Price each 1 to 3
HG8-15/ECO	15	120	136	90	25	8,2	90,91 €
HG8-18/ECO	18	144	160	100	25	11,7	119,76 €
HG8-20/ECO	20	160	176	120	30	14,6	134,96 €
HG8-24/ECO	24	192	208	150	30	21,7	178,68 €
HG8-25/ECO	25	200	216	150	30	23,3	191,37 €
HG8-28/ECO	28	224	240	170	30	29,5	218,95 €
HG8-30/ECO	30	240	256	190	30	34,4	242,79 €

All dimensions in mm

Altri prodotti...



GB5z

Vite a ricircolo di sfere, Dado cilindrico



PR40

Piede fissabile con snodo - poliammide, Ø 40



AKN

Giunto a soffietto Gerwah®, da 22 a 180Nm



BABTV

Ball lock pins lockable, Stainless steel



CHA

Cerniera, Robusta - Apertura 180°



TCC_SS

Tenditore, Inox



SBF

Sealed flange bearing unit for Food Industry, cover



CNA-CNG

Staffa di montaggio per molla a gas, Staffa di montaggio a squadra p...



RAS

Snodo angolare a 90° DIN71802, Inox



ZDB

Ingranaggio conico in plastica, 2:1



PRF_PSA

Rotella per profilo alluminio, Albero per



BMM

Manopola, zigrinata

Prodotti correlati