

Threaded Lock Pins

Ste

BABM

Steel

- Self-locking threaded lock pin
- Quick fastening
- Used for quick fastening, locking, adjusting, changing, clamping, connecting and securing
- Material :
 - Pin Stainless steel
 - Handle Black PA6
- Working T°: -30°C to +80°C

For tapped hole




Uses


- The segments retract when the button is pressed. Insert the pin into the threaded hole (this avoids the need to screw in a standard bolt). Once it is in place, release the button and tighten to secure it. To remove, unscrew by a quarter turn and remove the pin by pressing the button

Info

- Also exists in stainless steel



Typical application



DISCOUNTS

| | | | |
|-------|------|-----|------------|
| Qty | 1+ | 6+ | 10+ |
| Disc. | List | -5% | On request |

| Part number | ØD1 | L1 | ØD2 | ØD3 | ØD4 | L2 | L3 | L4 | Tightening torque* (Nm) | Clamping force* (Kn) | Shearing resistance two-shear* (kN) | Weight (g) | Price each 1 to 5 |
|-------------|-----|----|-------|-----|------|------|-------|----|-------------------------|----------------------|-------------------------------------|------------|-------------------|
| BABM8-10 | M8 | 10 | 6,62 | 40 | 21,6 | 23,8 | 58,4 | 8 | 3,5 | 2,3 | 12,7 | 86 | |
| BABM8-20 | M8 | 20 | 6,62 | 40 | 21,6 | 33,8 | 68,4 | 8 | 3,5 | 2,3 | 12,7 | 90 | |
| BABM8-30 | M8 | 30 | 6,62 | 40 | 21,6 | 43,8 | 78,4 | 8 | 3,5 | 2,3 | 12,7 | 93 | |
| BABM10-10 | M10 | 10 | 8,35 | 40 | 21,6 | 26,0 | 60,6 | 10 | 3,5 | 2,0 | 20,6 | 93 | |
| BABM10-20 | M10 | 20 | 8,35 | 40 | 21,6 | 36,0 | 70,6 | 10 | 3,5 | 2,0 | 20,6 | 94 | |
| BABM10-30 | M10 | 30 | 8,35 | 40 | 21,6 | 46,0 | 80,6 | 10 | 3,5 | 2,0 | 20,6 | 99 | |
| BABM12-15 | M12 | 15 | 10,07 | 40 | 21,6 | 34,0 | 68,6 | 12 | 3,5 | 1,8 | 30,4 | 99 | |
| BABM12-30 | M12 | 30 | 10,07 | 40 | 21,6 | 49,0 | 83,6 | 12 | 3,5 | 1,8 | 30,4 | 108 | |
| BABM12-50 | M12 | 50 | 10,07 | 40 | 21,6 | 69,0 | 103,6 | 12 | 3,5 | 1,8 | 30,4 | 122 | |
| BABM16-15 | M16 | 15 | 13,80 | 40 | 21,6 | 34,0 | 68,6 | 12 | 3,5 | 1,5 | 62,9 | 116 | |
| BABM16-30 | M16 | 30 | 13,80 | 40 | 21,6 | 49,0 | 83,6 | 12 | 3,5 | 1,5 | 62,9 | 133 | |
| BABM16-50 | M16 | 50 | 13,80 | 40 | 21,6 | 69,0 | 103,6 | 12 | 3,5 | 1,5 | 62,9 | 155 | |

Dimensions in mm * Average value established in trials

** Shearing resistance similar to DIN 50141; values apply to applications in plugged condition (without applied tightening torque)

Altri prodotti...



CLSCLP

Forcella serie corta,
Corta acciaio



AC144

Piastrina di riscontro
piatta per chiusura,
22mm



CHAE4060PA

Cerniera ad avvitare
estetica asimmetrica,
Poliammide



SBF

Sealed flange bearing
unit for Food Industry,
cover



PRF4545

Profilato alluminio
standard, 45 x 45 mm



SLBE

Pistoncino a molla,
Anello distanziatore
per pistoncino a molla
SLB



RT70

Calettatore di
bloccaggio, Coppia
media/elevata



DILC

Indexing plunger with
cam, with cam



SLV

Attrezzo di bloccaggio
a leva verticale, A
leva verticale - acciaio



PTR

Pignone tendicatena,
Per applicazioni
correnti



SCA

Serracavo, Acciaio



ZG1

Ingranaggio dritto in
plastica, Plastica
lavorata (delrin)

Prodotti correlati