

- Ideal for moving bottles and metal cans at high speeds

- Smooth surface with no backlash
- Non knurled pin


- Materials:

Plates: low friction acetal

Pin: stainless steel 304

- Operating temp.: -40°C to +85°C (+70°C in humid environments)

- Length 3048mm (80 plates)





Advantages


- In most applications no lubrication is necessary

Associated products

- Drive sprocket **PT820**
- Idler sprocket **PR820**
- Idler **DBL820**



Direction of travel →



DISCOUNTS

Qty.	1+	5+	10+
Disc.	List	-5%	On request


Part number	Width K (mm)	Length (mm)	Breaking load (N)	Weight (kg/m)	Price each 1 to 4
CAP820-82	82,5	3048	3200	0,83	80,63 €
CAP820-114	114,3	3048	3200	1,03	102,69 €

Dimensions in mm

Altri prodotti...



HTD5M_15
Puleggia dentata di trasmissione tipo HTD, HTD5 Alluminio



AC
Piastrina di riscontro, 15mm



SEV
Attrezzo di bloccaggio a tirante, A tirante verticale - acciaio




VPR
Vite ad alette Hygienic Usit®, Inox



SSDB
Ingranaggio conico inox, 2:1



PAT123
Piede snodato con base lamiera Ø123, Ø123



GPLny
Scovolo, nylon



QTR
Cuscinetto a rulli conici, Acciaio



DILC
Indexing plunger with cam, with cam



TUBE25_25
Tubo quadrato, Alluminio



CQA30
Slitta di regolazione miniatura, 30



ASH
Anello di sollevamento, dritto a saldare

Prodotti correlati



PT820
Pignone di trazione, Serie 820 e 815



PR820
Ruota di rinvio, Serie 820 e 815



CAP815
Catena a tapparella dritta, Stretta serie 815



DBL820
Rotella per catena, Serie 820 e 815