

Master link assembly **high resistance**



MTT_{HR}

High strenght alloy steel

- **Connecting link Rigging equipment**

- **Material:**

High strenght alloy steel
grade 80 red painted

Stamping


- CE, SWL, manufacturer, grade

Info

- Generally conform to norm EN 1677- 4+A1

- The Breaking load is calculated by multipling
the WLL by a safety factor of 4"

*High
resistance*



DISCOUNTS

Qty	1+	6+	20+	30+
Disc.	List	-10%	-20%	On request

Part number	WLL (kg)	A	B	ØD	A1	B1	ØD1	Weight (kg)	Stock*	Price each 1 to 5
MTT18-3150/HR	3,15	135	75	18	60	38	14	1,330		

*Dimensions in mm

Altri prodotti...




STL
Guida con spazzola,
Binario



CF
Perno folle, Standard -
acciaio



CHV
Motovariatore
meccanico, da 0,18 a
1,5kW



KSM
Dado cilindrico in
acciaio, Acciaio - 1
filetto



B_ECO
Ingranaggio conico -
Acciaio C43 - ECO, 1:1



BOX-TOR-INCH
Valigetta di
guarnizioni toriche in
nitrile, For fasteners
and fitting



NCT
Giunto di
collegamento, Ad
angolo fisso



PRF19_E
Squadra di giunzione,
PRF19 a PRF32




TB8
Cuscinetto assiale a
rulli cilindrici, Acciaio



UGH20
Unità di guida tipo H,
Per martinetti Ø20



CNA-CNG
Staffa di montaggio
per molla a gas,



ZR
Cremagliera in
plastica, Delrin

Prodotti correlati