

- Kit of assorted precision feelers for adjusting, equalising, fixing or positioning
- To be cut to form required
- Materials:
 - Steel 1.1274
 - Stainless steel 1.4310
 - Brass 2.0321

Advantage

- Wide range of thicknesses in each box allows accurate positioning for all applications

Applications

- Aligning workpieces before machining, aligning differently sized/shaped pieces, adjusting valve lash, wedging tools, adjusting bearings



DISCOUNTS

Qty	1+	3+	5+
Disc.	List	-5%	On request

Part number	Number		Material	Contents of box	Stock*	Price each 1 to 2
	Format	Sheets				
CLQ25-300-21/A	25x300	21	steel 1.1274	0,01/0,02/0,03/0,04/0,05/0,06/0,07/0,08/0,09/0,10/0,15/0,20/0,25/0,30/0,40/0,50/0,60/0,70/0,80/0,90/1,00	✓	48,05 €
CLQ50-300-25/A	50x300	25	steel 1.1274	0,01/0,02/0,03/0,04/0,05/0,06/0,07/0,08/0,09/0,10/0,12/0,15/0,18/0,20/0,25/0,30/0,35/0,40/0,45/0,50/0,60/0,70/0,80/0,90/1,00	✓	83,20 €
CLQ50-300-23/A	50x300	23	steel 1.1274	0,03/0,04/0,05/0,06/0,07/0,08/0,09/0,10/0,12/0,15/0,18/0,20/0,25/0,30/0,35/0,40/0,45/0,50/0,60/0,70/0,80/0,90/1,00	✓	68,99 €
CLQ100-500-9/SS	100x500	9	s/steel 1.4310	0,02/0,05/0,10/0,15/0,20/0,30/0,40/0,50/1,00	✓	99,51 €
CLQ100-500-11/SS	100x500	11	s/steel 1.4310	0,02/0,05/0,10/0,15/0,20/0,25/0,30/0,35/0,40/0,45/0,50	✓	100,78 €
CLQ100-500-11/SS2	100x500	11	s/steel 1.4310	0,50/0,55/0,60/0,70/0,75/0,80/0,85/0,90/0,95/1,00	-	227,97 €
CLQ150-500-10/SS	150x500	10	s/steel 1.4310	0,025/0,05/0,075/0,1/0,15/0,20/0,25/0,30/0,50	-	143,19 €
CLQ150-500-10/BR	150x500	10	brass 2.0321	0,025/0,05/0,075/0,1/0,15/0,20/0,25/0,30/0,50	-	167,98 €

*Depending on availability - Dimensions in mm

Altri prodotti...



INStool
Boccola autofilettante
- Attrezzo, Strumento di posa




MCL
Manicotto cilindrico
maschiato, Cilindrico - inox



ACL-PLAngle
Elementi di giunzione,
Collegamento angolare




CHTRB
Riduttore a rinvio
angolare a L o a T,
fino a 87,3 Nm



PF20NM
Riduttore a ruota e
vite senza fine, fino a
5 Nm



PRF_GAL
Rotella per profilo
alluminio, Kit di
fissaggio per rotella
concentr...



RPP8
Cinghia di
trasmissione RPP,
RPP8



BAG
Anello di bloccaggio in
acciaio, Acciaio



BMF
Manopola, Zigrinata -
Cieco



HBM
Guida su semi-binari,
Boccola di regolazione



PTAF80-PAMF80
Piede fissabile con
base lamiera Ø80, Ø
80



PM3
Coppia ruota e vite
senza fine, Acciaio
trattato

Prodotti correlati



CLQ
Cuscinetti a sfere -
Accessorio, Spessori
metallici centesimali a
na...