



# Adjustable clamp


For rod or tube

NSR


- Holds cylindrical sections (rods, tubes...)
- Materials:  
Wing knob: thermosetting plastic  
Colour: dark grey  
Screw: steel, resistance class 5.8  
Other parts: high-resistance anodised aluminium

## Advantages

- Each side adjusts individually, no bearing
- Simple construction using wing nuts
- Tightens quickly



Example of use



## DISCOUNTS

Qty.	1+	10+	30+
Disc.	List -5%	On request	

Part number	ØD	ØD1	ØD2	L	L1	L2	L3	L4	H	H1	Weight (kg)	Stock*	Price each 1 to 9
NSR-8	8	28	M8	90	42	24	24	13	50	8,5	0,086	-	37,80 €
NSR-10	10	32	M8	100	52	24	32	15	50	9,5	0,124	✓	39,57 €
NSR-12	12	36	M8	104	56	24	34	17	50	10,5	0,157	✓	45,30 €
NSR-16	16	45	M10	142	72	35	44	22	75	13,5	0,345	✓	57,68 €
NSR-20	20	74	M10	172	102	35	62	30	75	22,0	1,110	✓	86,35 €

\*Dans la limite du disponible - Dimensions en mm

## Altri prodotti...



HLU

Volantino con razze,  
Alluminio



BUH77

Motoriduttore DC 12V  
e 24V DC, da 0.1 a 2  
Nm



GMK17\_R

Guida prodotto  
laterale tonda, Per  
imbottigliamento e  
imballaggio




PGNT

Impugnatura  
termoplastica a T, Con  
perno filettato



BPQ

Quadro linear ball  
bearing unit, Included  
4 linear ball bearings



PRF4545r90

Profilato alluminio  
standard, 45 x 45 mm  
- R90°




T5courroie

Cinghia di  
posizionamento T, T5  
Poliuretano armatura  
in acciaio



MCL

Manicotto cilindrico  
maschiato, Cilindrico -  
acciaio



ACLBTS

Sistema di chiusura  
per profili alluminio,  
Squadra per blocca




HFL

Ruota libera,  
Combinata ad aghi



HG8-ECO

Ingranaggio dritto  
acciaio, Acciaio C45



G0

Ingranaggio dritto  
acciaio, Acciaio  
20NCD2

## Prodotti correlati



NSA

Connettore rinvio  
d'angolo, Articolato



NJM

Connettore rinvio  
d'angolo, Multiplo