

- Kit of assorted precision feelers for adjusting, equalising, fixing or positioning
- To be cut to form required
- Materials:
 - Steel 1.1274
 - Stainless steel 1.4310
 - Brass 2.0321

Advantage

- Wide range of thicknesses in each box allows accurate positioning for all applications

Applications

- Aligning workpieces before machining, aligning differently sized/shaped pieces, adjusting valve lash, wedging tools, adjusting bearings



DISCOUNTS

Qty	1+	3+	5+
Disc.	List	-5%	On request

Part number	Number		Material	Contents of box	Stock*	Price each 1 to 2
	Format	Sheets				
CLQ25-300-21/A	25x300	21	steel 1.1274	0,01/0,02/0,03/0,04/0,05/0,06/0,07/0,08/0,09/0,10/0,15/0,20/0,25/0,30/0,40/0,50/0,60/0,70/0,80/0,90/1,00	✓	48,05 €
CLQ50-300-25/A	50x300	25	steel 1.1274	0,01/0,02/0,03/0,04/0,05/0,06/0,07/0,08/0,09/0,10/0,12/0,15/0,18/0,20/0,25/0,30/0,35/0,40/0,45/0,50/0,60/0,70/0,80/0,90/1,00	✓	83,20 €
CLQ50-300-23/A	50x300	23	steel 1.1274	0,03/0,04/0,05/0,06/0,07/0,08/0,09/0,10/0,12/0,15/0,18/0,20/0,25/0,30/0,35/0,40/0,45/0,50/0,60/0,70/0,80/0,90/1,00	✓	68,99 €
CLQ100-500-9/SS	100x500	9	s/steel 1.4310	0,02/0,05/0,10/0,15/0,20/0,30/0,40/0,50/1,00	✓	99,51 €
CLQ100-500-11/SS	100x500	11	s/steel 1.4310	0,02/0,05/0,10/0,15/0,20/0,25/0,30/0,35/0,40/0,45/0,50	✓	100,78 €
CLQ100-500-11/SS2	100x500	11	s/steel 1.4310	0,50/0,55/0,60/0,70/0,75/0,80/0,85/0,90/0,95/1,00	-	227,97 €
CLQ150-500-10/SS	150x500	10	s/steel 1.4310	0,025/0,05/0,075/0,1/0,15/0,20/0,25/0,30/0,50	-	143,19 €
CLQ150-500-10/BR	150x500	10	brass 2.0321	0,025/0,05/0,075/0,1/0,15/0,20/0,25/0,30/0,50	-	167,98 €

*Depending on availability - Dimensions in mm

Altri prodotti...



INStool

Boccola autofilettante
- Attrezzo, Strumento
di posa



AT5M AT10M

Cinghia aperta al
metro tipo AT, AT5
Poliuretano armatura
in acciaio



BH01

Cuscinetto radiale
flangiato, Montaggio :
pressione e colla



BFDdII

Boccola di fermo per
perno ad innesto,
Acciaio nichelato




GMC_GMK_BR

Morsetto porta guide,
Piatto o tondo



PF40

Riduttore a ruota e
vite senza fine, fino
a18 Nm



RPP8

Cinghia di
trasmissione RPP,
RPP8



RPCpl

Ruota girevole con
piastra, Acciaio -
Poliammide



PRF-CHAR-POU

Attrezzi, Carrello
attrezzi



CHM110

Riduttore a ruota e
vite senza fine, fino a
110 Nm



BFM

Dado trapezoidale,
Bronzo - 1 filetto



HSE-HSB

Distanziatore
esagonale, Acciaio

Prodotti correlati



CLQ

Cuscinetti a sfere -
Accessorio, Spessori
metallici centesimali a
na...