Fixed anti-vibration foot

For loads up to 35 000 N

PAV

- ***Adjustable anti-vibration foot***
- *Fine thread for levelling*
- *Materials:*
  Body: Chromed sheet steel
  Spindle: Chromed steel
  Base: Rubber NBR 80 shore




Applications

- *Machine tools, presses, injection machines, compressors.*

Info

- *Supplied with 1 nut and 1 washer*



IN STOCK*
Otherwise contact us

DISCOUNTS

Qty	1+	6+	10+	15+
Disc.	List	-5%	-10%	On request

Part number	ØD	ØF	B	ØD1	SW	G	H	Max load Dynamic (N)	Max load Static (N)	Price each 1 to 5
PAV80-M12C	80	M12x1,25	87	60	8	40-50	136	2500	5000	43,91 €
PAV120-M16C	120	M16x1,5	93	80	9	45-58	150	4000	10000	74,04 €
PAV160-M20C	160	M20x1,5	125	100	12	53-65	190	9000	20000	122,40 €
PAV200-M20C	200	M20x1,5	125	130	12	69-82	207	15000	35000	168,22 €

**Depending on availability - Dimensions in mm*