


**NEW!****DISCOUNTS**


Qty	1+	10+	20+	30+	50+
Disc.	List	-5%	-10%	-15%	On request

Part number	Corresponding diameter D1	Price each 1 to 9
FR-M5/TOOL	M5	28,84 €
FR-M6/TOOL	M6	29,80 €
FR-M8/TOOL	M8, M8x1	31,08 €
FR-M10/TOOL	M10, M10x1,25	33,32 €
FR-M12/TOOL	M12, M12x1,25	35,99 €


Assembly




- 1.*
Drill the pilot hole or rebores the old thread with a starting taper (82° - 100°)



- 2.*
Tap the required thread using a standard tap.




3.
Screw in the thread inserts. These should finish below the top surface of the material (0.3 to 0.7mm).




4.
Insert the keys using the supplied tool, tapping gently with a hammer.

Steps 1+2. Refer to the parts table for the dimensions.


Disassembly




- 1.*
Rebores the remaining material between the keys and threads to the depth indicated



2.
Bend the keys towards the centre until they break



3.
Remove the thread inserts using the extraction tool



4.
Mount the new thread inserts in the original threads


** Steps 1. Refer to the parts table for the dimensions*

Altri prodotti...



WS10

Guida modulabile
Drylin® W, Binario



BTC

Tappo per tubo
quadrato, Standard



DFG

Ventosa, silicone



PITA

Pistoncino a molla,
con maniglia a T



PDD

Pressore a molla
sensore di
rilevamento, Con asta
di comando per int...



GAL48_OMNI

Ruota per
trasportatore,
Omnidirezionale



VCMB

Vite di giunzione
metallo/legno, Acciaio



BSCm

Manopola, Con coppia
regolabile



V3RA_PT

Volantino a tre razze,
Poliammide



HG6

Ingranaggio dritto
acciaio, Acciaio
20NCD2



PTA100

Piede snodato con
base stampata Ø100,
Ø 100



PO

Maniglia a ponte -
Multi-settore, Foro
liscio

Prodotti correlati



FR

Inserti filettati, Acciaio



FRss

Inserti filettati, Inox