

Levelling foot stainless steel **for robot**

PMN

Max load up to 45 000N

- Foot with stainless steel base plate

- Materials:


- AISI 304 stainless steel base
- AISI 304 stainless steel rod
- NBR FDA-approved rubber foot, 90° Shore hardness

Advantages


- Excellent value for money
- Foot offers exceptional resistance to machine slippage or movement

Installation

- Position the levelling foot at the intended location for your machine
- Once the levelling foot and the machine are correctly positioned, drill into the floor using the through-hole located between the rod and the base
- Insert a threaded rod and secure it with resin or a wall plug
- This results in a levelling foot that is fully self-supporting, with no visible holes, and which can be adjusted for height



Installation



DISCOUNTS

Qty	1+	5+	8+
Disc.	List	-5%	On request

Références	B	A	M	G	H	H1	ØD	ØD1	Max load (N)	Price each 1 to 4
PMN120-160/SS	121	31	M30x1.5	18	152	160	120	19	45000	

Dimensions in mm

Altri prodotti...



F7-SF-SM
Visualizzatore multifunzione,
Supporto - montaggio
frontale



PSG35
Ingranaggio dritto di
precisione, Inox 316



INO
Ingranaggio interno,
Acciaio 20NCD2



NAST
Rotelle, Con anello
interno



ACLERP
Rulliera, Con guida
laterale



WJUM10
Pattino Drylin® W,
Pattino



EMR
Volantino zigrinato a
serraggio rapido,
Zigrinato



UTKpwr
Guida lineare
Utilitrack®, Profilo
guida a V



NPTF20
Morsetto di
collegamento, Fisso
Ø10 a Ø14



SDG
Supporto con tirante
ad occhio, Plastica



CFUURSS
Perno folle inox,
Standard - inox



SUPss
Calettatore di
bloccaggio
autocentrante inox,
Senza ghiera

Prodotti correlati