


## Module 8,0

### C45 Steel

- Economical gear range
- Pressure angle 20°
- Material:  
C45 steel UNI7845

#### Info.

- \* Pre-bore information is given as a guide only and may vary between batches
- Gear should be finished to suit the application
- **We are unable to modify these gears**



**economic series**

#### DISCOUNTS

Qty	1+	4+	10+
Disc.	List	-5%	On request

Part number	Z Teeth	ØP PCD	ØD External	ØM Hub	ØA Pre-bore	Weight (kg)	Price each 1 to 3
HG8-15/ECO	15	120	136	90	25	8,2	90,91 €
HG8-18/ECO	18	144	160	100	25	11,7	119,76 €
HG8-20/ECO	20	160	176	120	30	14,6	134,96 €
HG8-24/ECO	24	192	208	150	30	21,7	178,68 €
HG8-25/ECO	25	200	216	150	30	23,3	191,37 €
HG8-28/ECO	28	224	240	170	30	29,5	218,95 €
HG8-30/ECO	30	240	256	190	30	34,4	242,79 €


All dimensions in mm

## Altri prodotti...



CHAGC-AL

Cerniera ad avvitare,  
Sfilabile



RPPM

Cinghia aperta al  
metro tipo RPP, RPP8  
Poliuretano armatura  
in acciaio



CHV

Motovariatore  
meccanico, da 0,18 a  
1,5kW



PRF\_VTM

Fissaggio, Vite testa  
martello



CHA138

Cerniera ad avvitare,  
138 gradi



PX\_PO

Maniglia -  
movimentazione  
manuale, con piastra  
posteriore



CHT

Motore AC asincrono  
trifase, 0.12 a 0.22kW



RPCtc

Ruota girevole a foro  
centrale, Acciaio -  
Poliammide - a doppio  
bloc...



PRF\_PSA

Rotella per profilo  
alluminio, Albero per  
guida



EP7

Indicatore di posizione  
elettronico, 5 cifre



RFK38C

Riduttore ipoide inox,  
fino a 200 Nm



RGS

Giunto senza gioco  
Rotex® GS, da 0.5 a  
190Nm

**Prodotti correlati**