

PERIFLEX® elastic coupling

PNA

Replacement tyre

- Tyre for PERIFLEX® coupling

- Replace the tyre without dismantling the machine
- Material natural rubber Tyre R (NR) equipped with disposed material in R
- Quality tyre X(1) with inserts mounted in X pattern



Assembly

- The elastic coupling is delivered pre-assembled. To mount the coupling, remove the tyre and place the hubs and locking assemblies on their respective shafts. Bring the two assemblies together respecting the distance "O" and aligning the two hubs with a straight edge or template.
- Place the tyre between the two hubs ensuring there is minimum radial backlash (2-15mm depending on the size of the coupling). Then bring the two locking assemblies together, tightening pairs of diametrically opposite screws to the prescribed torque. As the rubber may decompress with time, re-check the torque after a few hours.

SAVE MONEY !
Only change the tyre

DISCOUNTS

Qty.	1+	5+	10+
Disc.	List	-3%	On request

Part number spare tyre	for PERIFLEX® coupling part number	Type of tyre	Stock*	Price each 1 to 4
203R	PNA2-203	R	✓	86,27 €
206R	PNA6-206	R	✓	105,43 €
210R	PNA16-210	R	✓	159,10 €
214R	PNA40-214	R	✓	247,29 €
218R	PNA63-218	R	✓	256,88 €
414X	PNA40-214	X	-	249,22 €
418X	PNA63-218	X	-	274,13 €

*Depending on availability - Dimensions in mm

Altri prodotti...



CAP815

Catena a tapparella dritta, Stretta serie 815



PRF_ART

Cerniere e giunti, Con maniglia di serraggio



BPPE

Sfera portante, Leggero



CFF

Testa a snodo femmina DIN ISO12240-4, Acciaio / bronzo



HTD8M_20

Puleggia dentata di trasmissione tipo HTD, HTD8 Ghisa



PTAf80-PAMF80

Piede fissabile con base lamiera Ø80, Ø 80



DOG258

Motoriduttore DC 12V e 24V DC, da 12 a 15 Nm



M1

Coppia ruota e vite senza fine, Bronzo



SBF

Open flange bearing unit for food industry,



GO

Ingranaggio dritto acciaio, Acciaio



SLBWSS

Pistoncino a molla, Da saldare - inox



DBL820

Rotella per catena, Serie 820 e 815

Prodotti correlati



PNA

Giunto elastico PERIFLEX®, Giunto completo