

PRES

Accessories for PRES-3HR and PRES-4HR presses

These accessories are only suitable for use with the PRES-3HR and PRES-4HR presses


PRES-PMB: Micrometric adjustment PMB.
Bottom dead centre adjustment system, graduated every 0.02 mm

PRES-TE: Slot nuts for securing tools in the T slot

PRES-ER25: Collet chuck
Collet chuck with ER25 collet for shanks from \varnothing 1.5 to \varnothing 16 mm (Other diameters between 1.5 and 16 mm available on request)



PRES-PMB



PRES-TE



PRES-ER25

DISCOUNTS

Qty	1	2+	4+
Disc.	List	-3%	On request

Part number	Type	For shank diameter	Price each
PRES-PMB	Micrometric adjustment (0.02mm)	-	403,32 €
PRES-TE	Set of slot nuts for T profile slots	-	26,30 €
PRES-ER25-1.5	tool holder	1,5	467,62 €
PRES-ER25-2	tool holder	2	467,62 €
PRES-ER25-4	tool holder	4	467,62 €
PRES-ER25-6	tool holder	6	467,62 €
PRES-ER25-8	tool holder	8	467,62 €
PRES-ER25-10	tool holder	10	467,62 €
PRES-ER25-12	tool holder	12	467,62 €
PRES-ER25-14	tool holder	14	467,62 €
PRES-ER25-16	tool holder	16	467,62 €

Dimensions in mm

Altri prodotti...



FF30

Riduttore ad alberi paralleli, da 21.50 a 83 Nm



RPCtc

Ruota girevole a foro centrale, Acciaio - Poliammide - a doppio bloc...



PTA40

Articulated foot with solid base foot Ø 40, 30000N



DCA

Ventosa, Gomma naturale



PFM

Piede senza snodo, Lamiera modellata



G2

Ingranaggio dritto acciaio, Acciaio 20NCD2



P55

Riduttore a ruota e vite senza fine, fino a 57 Nm



ACLEPP

Angolare, 4 fori



AC156-157

Riscontro per chiusura a leva rigida ad



M1

Coppia ruota e vite senza fine, Acciaio



PM2

Coppia ruota e vite senza fine, Acciaio



MEB

Ingranaggio conico in plastica stampata, 1:1

Prodotti correlati



PRES3HR

Pressa manuale da banco, Pressione fino a 400kg



PRES4HR

Pressa manuale da banco, Pressione fino a 600kg