

Stainless steel articulated foot Ø50 **Sta Stock**

PRS50

Maximum load 15,000N


- Levelling foot
- With non-slip base
- Materials:
 - Base: stainless steel AISI 304
 - Spindle: stainless steel AISI 304 (nut not supplied)
 - Sole: NBR rubber (Shore hardness 70)

Solid stainless steel



Advantages

- Articulated spindle allows auto-alignment with the floor
- Sole material ensures flexibility and grip



DISCOUNTS

Qty	1+	6+	10+	15+
Disc.	List	-5%	-10%	On request

Part number	ØM	A	B	ØD	A/F	G	H	H1	Static load (N)	Stock*	Price each 1 to 5
PRS50-10-50	M10	28	50	50	14	16	78	81	15000	✓	39,86 €
PRS50-10-75	M10	28	75	50	14	16	103	106	15000	✓	42,49 €
PRS50-10-100	M10	28	100	50	14	16	128	131	15000	✓	44,96 €
PRS50-10-125	M10	28	125	50	14	16	153	156	15000	✓	47,41 €
PRS50-12-50	M12	28	50	50	14	16	78	81	15000	✓	39,86 €
PRS50-12-75	M12	28	75	50	14	16	103	106	15000	✓	42,49 €
PRS50-12-100	M12	28	100	50	14	16	128	131	15000	✓	44,96 €
PRS50-12-125	M12	28	125	50	14	16	153	156	15000	✓	47,41 €
PRS50-14-50	M14	28	50	50	14	16	78	81	15000	✓	39,86 €
PRS50-14-75	M14	28	75	50	14	16	103	106	15000	✓	42,49 €
PRS50-14-100	M14	28	100	50	14	16	128	131	15000	✓	44,96 €
PRS50-14-125	M14	28	125	50	14	16	153	156	15000	✓	47,41 €

*Depending on availability - Dimensions in mm

Altri prodotti...




SBF

Sealed flange bearing unit for Food Industry, cover



METC

Cuscinetto a collare ,
Bronzo autolubrificante
METAFRAM



CFC

Pressore a molla con
esagono incassato, A
contatto elettrico



LVT

Mini martinetto
motorizzato 4A, 4
ampere




PSG05S

Ingranaggio dritto di
precisione, Inox 316



PCLA_T

Maniglia a ripresa,
Plastica



BOX-TOR-TOOL

Valigetta di
guarnizioni toriche in
nitrile, Extraction
tools



MSP23

Inserto con piastrina a
incollare
Masterplate®,
Cilindrico Ø23 con...



GAL21

Ruota per
trasportatore, Plastica



DB

Ingranaggio conico in
acciaio, 2:1



HTD8M_50

Puleggia dentata di
trasmissione tipo



DB

Ingranaggio conico in
acciaio, 2:1

Prodotti correlati



PR550

Piede snodato tutto
inox Ø50, Ø 50



PAM_SS

Piede snodato con
base lamiera, Ø 30 &
40