

- ***Material*: iglidur® J**
- Yellow
- Working temperature: -50°C to +90°C (+60°C ideal, +120°C for short periods)
- Max. continuous speed:
  Rotating 1.5 m/s
  Oscillating 1.5 m/s
  Linear 8 m/s
- Pressure resistance:
  at +20°C 35 N/mm² (ideally 2 N/mm²)
- Friction coefficient
  dry 0.06-0.18
  greased 0.09
  water/oil 0.04
- **Not sold individually, please contact us for details**

Maintenance free





Assembly

- Recommended assembly tolerances shaft h9, housing bore-size H7
- Shaft treated 50 HRc, surface finish 0.8-2 µm

Options

- Bore diameter up to 70mm

DISCOUNTS

Qty	1+	10+	25+	50+	100+	200+	500+
Disc.	List	-10%	-25%	-40%	-50%	-60%	On request

Part number	Ød1	Ød2	Ød3 (d13)	b1 (h13)	b2 (-0,14)	f	Stock*	Price each 1 to 9
JFM0304-05	3 +0,014 +0,054	4,5	7,5	5	0,75	0,5	✔	2,42 €
JFM0405-06	4 +0,020 +0,068	5,5	9,5	6	0,75	0,5	✔	2,42 €
JFM0507-05	5 +0,020 +0,068	7,0	11,0	5	1,00	0,5	✔	2,42 €
JFM0608-06	6 +0,020 +0,068	8,0	12,0	6	1,00	0,5	✔	2,58 €
JFM0608-10	6 +0,020 +0,068	8,0	12,0	10	1,00	0,5	✔	2,69 €
JFM0810-06	8 +0,025 +0,083	10,0	15,0	6	1,00	0,5	✔	2,91 €
JFM0810-08	8 +0,025 +0,083	10,0	15,0	8	1,00	0,5	✔	3,01 €
JFM0812-06	8 +0,025 +0,083	12,0	16,0	6	1,00	0,5	✔	3,94 €
JFM1012-05	10 +0,025 +0,083	12,0	18,0	5	1,00	0,5	✔	2,96 €
JFM1012-09	10 +0,025 +0,083	12,0	18,0	9	1,00	0,5	✔	3,67 €
JFM1012-12	10 +0,025 +0,083	12,0	18,0	12	1,00	0,5	✔	3,73 €
JFM1012-15	10 +0,025 +0,083	12,0	18,0	15	1,00	0,5	✔	3,18 €
JFM1214-09	12 +0,032 +0,102	14,0	20,0	9	1,00	0,8	✔	3,55 €
JFM1214-12	12 +0,032 +0,102	14,0	20,0	12	1,00	0,8	✔	4,15 €
JFM1214-15	12 +0,032 +0,102	14,0	20,0	15	1,00	0,8	✔	4,38 €
JFM1416-12	14 +0,032 +0,102	16,0	22,0	12	1,00	0,8	-	4,09 €
JFM1416-17	14 +0,032 +0,102	16,0	22,0	17	1,00	0,8	✔	4,71 €
JFM1521-20	15 +0,032 +0,102	21,0	27,0	20	3,00	0,8	✔	7,10 €
JFM1618-17	16 +0,032 +0,102	18,0	24,0	17	1,00	0,8	✔	5,10 €
JFM1820-22	18 +0,032 +0,102	20,0	26,0	22	1,00	0,8	✔	5,43 €
JFM2023-21	20 +0,040 +0,124	23,0	30,0	21	1,00	0,8	✔	6,20 €
JFM2528-21	25 +0,040 +0,124	28,0	35,0	21	1,50	0,8	✔	6,79 €

**Depending on availability - Dimensions in mm*

Altri prodotti...



Supporto per sensore Ø18 e Ø20, ø18 e ø20



Chiusura a leva con serratura, Riscontro grezzo



Motoriduttore DC 12V e 24V DC, da 1.5 a 2 Nm



Ruota di precisione, Bronzo



Rinvio angolare a T, da 0.66 a 1.77 Nm



Perno di bloccaggio tipo ¼ di giro, ¼ di giro



Cinghia di trasmissione RPP, RPP3



Rinvio angolare a dentatura spiroidale, Fino a 182Nm



Piede fissabile con snodo - poliammide, Ø 123



Connettore rinvio d'angolo, Regolabile



Perno di fissaggio per morsetti, Filettato



Kit connettori per portacellule, Pre-assemblato

Prodotti correlati



Cuscinetto cilindrico , Polimero universale



Cuscinetto a collare , Polimero alimentare