

Master link assembly **high resistance**



MTT_{HR}

High strenght alloy steel

- Connecting link Rigging equipment

- Material:

High strenght alloy steel
grade 80 red painted

Stamping


- CE, SWL, manufacturer, grade

Info

- Generally conform to norm EN 1677- 4+A1

- The Breaking load is calculated by multipling
the WLL by a safety factor of 4"

High
resistance



DISCOUNTS

Qty	1+	6+	20+	30+
Disc.	List	-10%	-20%	On request

Part number	WLL (kg)	A	B	ØD	A1	B1	ØD1	Weight (kg)	Stock*	Price each 1 to 5
MTT18-3150/HR	3,15	135	75	18	60	38	14	1,330		

*Dimensions in mm

Altri prodotti...



Guida lineare
Utilitrack®, Ruota di
precisione a V in
acciaio



Piede snodato
semplice, Piede
inclinabile senza suola
antiscivolo



Pignone tendicatena,
Per applicazioni



Testa a snodo
femmina, Acciaio /
acciaio - Serie
economica



Cuscinetto a singola
corona di rulli
cilindrici, Anello
interno fiss...



Ingranaggio dritto
PRESTAZIONE, Acciaio



Valigetta di
guarnizioni toriche in
nitrile, 20.38 x
1.78mm a 50.16 ...



Piedino antivibrante
cilindrico, Inox



Fascette di serraggio,
Valigetta di fascette



Riduttore ipoide inox,
fino a 350 Nm



Accessori di
collegamento, Kit di
fissaggio



Anello di bloccaggio,
Acciaio

Prodotti correlati



Anello di
sollevamento,
Maschio



Anello di
sollevamento,
Femmina



Anello di
sollevamento,



Anello di
sollevamento, Acciaio