

# SteSta Pressed steel articulated foot Ø150

Accepts loads up to 40,000N

PTA150  
PTA150ss

- **Levelling foot**
- Brilliant finish (Sand-blasted finish for base of the stainless steel version)
- Materials:

#### Steel version:

Base: Chromed steel sheet C40

Rod: Chromed steel (nut not supplied)

Sole: Vulcanised rubber NBR hardness

80° Shore


#### Stainless steel version:

Base: 304 stainless steel, brilliant or sand-blasted finish

Rod: 304 stainless steel (nut not supplied)

Sole: Vulcanised rubber NBR hardness 80° Shore

Sand-blasted stainless-steel version



### Options

- Other rod sizes are available

### DISCOUNTS

Qty	1+	15+	20+	25+	40+
Disc.	List -5%	-10%	-15%		On request

Part number		ØD	ØF	B	A	A/F	G	H	Static load (N)	Price each 1 to 14
bright	sanded finish									
<b>Steel foot</b>										
PTA150-24-100	-	150	M24	100	44	24	35	144	40000	52,69 €
PTA150-24-150	-	150	M24	150	44	24	35	194	40000	55,61 €
PTA150-24-200	-	150	M24	200	44	24	35	244	40000	58,77 €
PTA150-24-250	-	150	M24	250	44	24	35	294	40000	61,72 €
PTA150-30-100	-	150	M30	100	44	30	35	145	40000	57,84 €
PTA150-30-150	-	150	M30	150	44	30	35	195	40000	59,65 €
PTA150-30-200	-	150	M30	200	44	30	35	245	40000	65,66 €
PTA150-30-250	-	150	M30	250	44	30	35	395	40000	73,95 €
<b>Stainless steel foot</b>										
PTA150-24-100/SS	PTA150-24-100/SS/SB	150	M24	100	49	20	35	149	40000	72,32 €
PTA150-24-150/SS	PTA150-24-150/SS/SB	150	M24	150	49	20	35	199	40000	76,29 €
PTA150-24-200/SS	PTA150-24-200/SS/SB	150	M24	200	49	20	35	249	40000	80,27 €
PTA150-24-250/SS	PTA150-24-250/SS/SB	150	M24	250	49	20	35	299	40000	84,26 €
PTA150-30-100/SS	PTA150-30-100/SS/SB	150	M30	100	50	26	35	150	40000	82,29 €
PTA150-30-150/SS	PTA150-30-150/SS/SB	150	M30	150	50	26	35	200	40000	88,11 €
PTA150-30-200/SS	PTA150-30-200/SS/SB	150	M30	200	50	26	35	250	40000	93,00 €
PTA150-30-250/SS	PTA150-30-250/SS/SB	150	M30	250	50	26	35	300	40000	97,86 €

All dimensions in mm

Fax **0 825 88 6000**  
Service 0,15 €/min  
+ prix appel

cial2@hpceurope.com

**HPC** SUPPLEMENT 2019

## Altri prodotti...



BFM2

Dado trapezoidale,  
Bronzo - 2 filetti



CLAT

Maniglia a ripresa  
Hygienic Usit®, Inox



CLQassortiment

Cuscinetto a sfera -  
Accessorio, Spessori  
metallici centesimali



PT821

Pignone di trazione,  
Serie 821 e 805



AT5M AT10M

Cinghia aperta al  
metro tipo AT, AT5  
Poliuretano armatura  
in acciaio



KH

Manicotto a sfera,  
Leggera



HTD14M\_55

Puleggia dentata di  
trasmissione tipo  
HTD, HTD14 Ghisa



MFBS

Giunto a soffietto  
Inox, Inox - con vite a  
pressione



CQA30

Slitta di regolazione  
miniatura, 30



H2

Ingranaggio elicoidale  
ad assi incrociati



BEAB

Manopola, stella, anti-  
bacterial



BHC

Vite a testa bombata  
BHC, Inox A2

## Prodotti correlati



PTA150

Piede snodato con  
base stampata Ø150,  
Ø 150



PTA150

Piede snodato con  
base stampata Ø150,  
Ø 150