



Adjustable clamp


For rod or tube

NSR


- Holds cylindrical sections (rods, tubes...)
- Materials:
Wing knob: thermosetting plastic
Colour: dark grey
Screw: steel, resistance class 5.8
Other parts: high-resistance anodised aluminium

Advantages

- Each side adjusts individually, no bearing
- Simple construction using wing nuts
- Tightens quickly



Example of use



DISCOUNTS

Qty.	1+	10+	30+
Disc.	List -5%	On request	


Part number	ØD	ØD1	ØD2	L	L1	L2	L3	L4	H	H1	Weight (kg)	Stock*	Price each 1 to 9
NSR-8	8	28	M8	90	42	24	24	13	50	8,5	0,086	-	37,80 €
NSR-10	10	32	M8	100	52	24	32	15	50	9,5	0,124	✓	39,57 €
NSR-12	12	36	M8	104	56	24	34	17	50	10,5	0,157	✓	45,30 €
NSR-16	16	45	M10	142	72	35	44	22	75	13,5	0,345	✓	57,68 €
NSR-20	20	74	M10	172	102	35	62	30	75	22,0	1,110	✓	86,35 €

*Dans la limite du disponible - Dimensions en mm

Altri prodotti...




CF
Perno folle, Standard -
acciaio



M0
Ruote per viti senza
fine, Bronzo



LSAG
Albero scanalato a
sfere, Carello - da 514
N a 15386 N



RPP14
Cinghia di
trasmissione RPP,
RPP14



SMS
Ingranaggio conico
spiroidale, 1:1



PTA40
Articulated foot with
solid base foot Ø 40,
3000N



SRG
Chiusura a leva
regolabile, Corsa da
78mm a 90mm



CHTRP
Riduttore a rinvio
angolare a L o a T,
fino a 87,3Nm



DOMI120
Accessori di
collegamento, Kit di



PRF-SCREEN-5
Screen support,
Support with 5 axes of



PRF_CH
Catena porta cavo,
Supplied in metre



PRS100
Piede snodabile tutto
inox Ø100, Ø 100

Prodotti correlati



NSA
Connettore rinvio
d'angolo, Articolato



NJM
Connettore rinvio
d'angolo, Multiplo