

# SteSta Pressed steel articulated foot Ø150

Accepts loads up to 40,000N

PTA150  
PTA150ss

- **Levelling foot**
- Brilliant finish (Sand-blasted finish for base of the stainless steel version)
- Materials:


**Steel version:**

Base: Chromed steel sheet C40  
Rod: Chromed steel (nut not supplied)  
Sole: Vulcanised rubber NBR hardness 80° Shore

**Stainless steel version:**

Base: 304 stainless steel, brilliant or sand-blasted finish  
Rod: 304 stainless steel (nut not supplied)  
Sole: Vulcanised rubber NBR hardness 80° Shore

Sand-blasted stainless-steel version



**Options**

- Other rod sizes are available

**DISCOUNTS**

Qty	1+	15+	20+	25+	40+
Disc.	List -5%	-10%	-15%		On request

Part number		ØD	ØF	B	A	A/F	G	H	Static load (N)	Price each 1 to 14
bright	sanded finish									
<b>Steel foot</b>										
PTA150-24-100	-	150	M24	100	44	24	35	144	40000	52,69 €
PTA150-24-150	-	150	M24	150	44	24	35	194	40000	55,61 €
PTA150-24-200	-	150	M24	200	44	24	35	244	40000	58,77 €
PTA150-24-250	-	150	M24	250	44	24	35	294	40000	61,72 €
PTA150-30-100	-	150	M30	100	44	30	35	145	40000	57,84 €
PTA150-30-150	-	150	M30	150	44	30	35	195	40000	59,65 €
PTA150-30-200	-	150	M30	200	44	30	35	245	40000	65,66 €
PTA150-30-250	-	150	M30	250	44	30	35	295	40000	73,95 €
<b>Stainless steel foot</b>										
PTA150-24-100/SS	PTA150-24-100/SS/SB	150	M24	100	49	20	35	149	40000	72,32 €
PTA150-24-150/SS	PTA150-24-150/SS/SB	150	M24	150	49	20	35	199	40000	76,29 €
PTA150-24-200/SS	PTA150-24-200/SS/SB	150	M24	200	49	20	35	249	40000	80,27 €
PTA150-24-250/SS	PTA150-24-250/SS/SB	150	M24	250	49	20	35	299	40000	84,26 €
PTA150-30-100/SS	PTA150-30-100/SS/SB	150	M30	100	50	26	35	150	40000	82,29 €
PTA150-30-150/SS	PTA150-30-150/SS/SB	150	M30	150	50	26	35	200	40000	88,11 €
PTA150-30-200/SS	PTA150-30-200/SS/SB	150	M30	200	50	26	35	250	40000	93,00 €
PTA150-30-250/SS	PTA150-30-250/SS/SB	150	M30	250	50	26	35	300	40000	97,86 €

All dimensions in mm

Fax **0 825 88 6000**  
Service 0,15 €/min + prix appel

cial2@hpceurope.com

**HPC** SUPPLEMENT 2019

## Altri prodotti...



PPG

Pistoncino a molla,  
Con flangia di  
fissaggio orizzontale



FDSQ

Flexible drive shaft,  
Masterflex® Steel,  
with PVC casing



PW\_PWG05

Vite senza fine di  
precisione, Acciaio



CABma

Manicotto ovale per  
cavo, Per la  
crimpatura di un cavo  
in acciaio



SHW

Rondella semplice ,  
Inox A2



VPSS

Volantino a 6 lobi,  
Duroplast - Inox



TIFss

Tirante tutto filetto -  
DIN976A, Inox




KB\_OP

Manicotto a sfere di  
precisione, Di  
precisione - acciaio



PCS62SS

Pignone a catena -  
Inox, 15.875mm (DIN  
08B-1)




GPLac

Scovolo, acciaio



MEB

Ingranaggio conico in  
plastica stampata, 1:1



PO

Maniglia a ponte -  
Multi-settore, Foro  
liscio

## Prodotti correlati



PTA150

Piede snodato con  
base stampata Ø150,  
40000N



PTA150

Piede snodato con  
base stampata Ø150,  
40000N



PTA100

Piede snodato con  
base stampata Ø100,  
15000N