

- **Swivelling mounting foot with steel mounting plate**

- **Materials:**

Base - chromed steel plate

Threaded shaft - chromed steel

**Usage**

- The threaded shaft is free to rotate


- A nut under the mounting base allows both rotation and angular inclination (+/-4°) movement to be restricted and means these feet can be used to support posts with recessed holes or mounting plates used with a nut and locknut.

- Angular blocking reduces noise and any lever effect on the mountings (avoids risk of being pulled out)

**Advantage**

- Ideal for floor mounting robots and also increased speed of production

**Economical**



Mounting bracket

Blind hole

**DISCOUNTS**

Qty	1+	6+	10+	15+	20+
Disc.	List	-5%	-10%	-15%	On request

Part number	ØM	B	S	A	SW	G	H	Static load (N)	Price each 1 to 5
PARF110-16-150	M16	150	4	41	17	19	191	25000	19,01 €
PARF110-16-200	M16	200	4	41	17	19	241	25000	20,06 €
PARF110-20-150	M20	150	4	42	17	19	192	25000	21,31 €
PARF110-20-200	M20	200	4	42	17	19	242	25000	23,07 €
PARF110-24-150	M24	150	4	43	20	19	193	30000	25,28 €
PARF110-24-200	M24	200	4	43	20	19	243	30000	27,86 €

Dimensions in mm

**0 825 88 6000**  
Service 0,15 € / min  
+ prix appel

## Altri prodotti...



Coppia ruota e vite senza fine, Plastica lavorata (delrin)



Riduttore coassiale, da 60 a 140 Nm



Crema di sezione metrica, Acciaio



Unità di guida per cilindrico, Cuscinetto lungo



Molla di compressione conica, Conica



Guida lineare a sfere - Sfere inox, Carello - da 516 N a 8396 N



Calettatore di bloccaggio, Coppia media/elevata



Anello di sollevamento, Orientabile maschio inox



Riduttore inox a ruota e vite senza fine,



Serracavo, Acciaio



Boccola scanalata Inox, Inox



Attacco per forcella, Corta inox

## Prodotti correlati



Piede senza snodo, Con foro per fissaggio



Piede fissabile con base lamiera Ø100, Ø 100



Piede senza snodo, Piede snodato oscillante fissabile Ø80