





### Advantages

- No maintenance required
- Low coefficient of friction
- Cost effective
- Robust
- Rigid
- Easily installed
- Wear resistant
- Materials:  
 Sliding mechanism: iglidur®  
 Ring: hard anodised aluminium  
 Screws: stainless steel




Smooth hole


### Tipping dependent on overturning torque



### Required torque for torque load






### Required torque for eccentric loads



Part number	Weight (kg)	Axial load rating, static (N)	Axial load rating, dynamic (N)	Axial load rating, dynamic (N)	Radial load rating, dynamic (N)	Rotary speed limit, dry (1/min)	Rigidity, axial (N/μm)	Rigidity, radial (N/μm)	Max. permitted Overturning torque (Nm)	Dimensions in mm		
										R1	R2	B
PRT01-30	0,4	27 000	7 000	5 000	1 500	250	-	-	200	41	29,0	4,5
PRT01-60	1,1	50 000	15 000	10 000	3 000	200	300	65	800	65	51,5	4,5
PRT01-100	1,3	55 000	16 000	16 000	5 000	150	400	65	1 500	80	69,0	5,5
PRT01-200	3,2	100 000	30 000	35 000	10 000	80	500	65	3 800	137	123,0	7,0

Dimensions in mm



**New sizes**

## DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-5%	On request

Part number	ØD	ØD1	Ød1	Ød	ØD2	H	h	T1	T2	S1	S2	K1		Price each
												for screw	1 to 4	
PRT01-20	80	70	31	20	60	24	8	3 x 120°	6 x 60°	M4	4,5	DIN 7984	M4	164,37 €
PRT01-30	100	91	42,5	30	82	29	10	8 x 45°	8 x 45,0°	M4	4,5	DIN 7984	M4	182,06 €
PRT01-50	150	135	65	50	120	33	10	8 x 45°	16 x 22,5°	M6	6,6	ISO 4762	M6	251,59 €
PRT01-60	160	145	74,0	60	130	33	10	10 x 36°	20 x 18,0°	M5	5,5	DIN 912	M5	274,50 €
PRT01-100	185	170	112,0	100	160	34	12	12 x 30°	16 x 22,5°	M5	5,5	DIN 912	M5	506,51 €
PRT01-150	250	235	165	150	220	35	12	12 x 30°	16 x 22,5°	M6	5,5	ISO 4762	M5	701,18 €
PRT01-200	300	285	215,0	200	274	38	15	12 x 30°	16 x 22,5°	M6	7,0	DIN 912	M6	903,83 €

Dimensions in mm

## Altri prodotti...



BAP25

Anello di bloccaggio,  
Ø25 - Ø40



SVT15

Martinetto a vite - Vite  
traslante, Vite  
traslante



ACLBMC

Supporto per sensore  
per profili alluminio,  
Porta cellula



BPM-Z

Pressore a molla con  
intaglio e puntale a  
sfera, Corpo plastica  
+ sf...



BLHB40

Rinvio angolare ad  
albero cavo, fino a  
10.3 Nm



SEH

Attrezzo di bloccaggio  
a tirante, A tirante -  
inox



SDB

Pistoncino a molla -  
Supporto, fissaggio  
perpendicolare alla  
serratura



PO

Maniglia a ponte -  
Multi-settore, Foro  
cieco maschiato



SPIT

Piede senza snodo,  
Con foro per fissaggio



PTA150

Piede snodato con  
base stampata Ø150,



EBM

Cavalletto in acciaio,  
Acciaio



BAB

Perno autobloccante a  
sfere, Inox temprato

## Prodotti correlati



PRT-TO

Corona girevole  
Iglidur®, Con  
dentatura esterna-  
Iglidur®, allumini...