

# Locking castor with central hole



## RIM

## For loads up to 1000kg



- A combination of a swivel castor and an adjustable locking support
- Used to easily support and moving machines or other heavy equipment and then positioning them in a very stable manner.
- Installation starts by lowering the locking support using a nut.
- With the wheel no longer resting on the ground, the supported unit can be levelled despite any irregularities in the floor.
- Operating temperature range: -30 to +80°C

### Materials

- Polyamide central control cross nut
- Anti-skid rubber mount allowing absorption of vibration and noise
- Body: Moulded cast aluminium body, hammered ivory paint finish
- Swivel system provided by 2 ball rings
- Mounting plate has a threaded central hole, threaded rod and nut supplied.
- Wheel: Black polyamide Shore D 70



Adjusting nut



### DISCOUNTS

Qty	1+	5+	14+
Disc.	List	-5%	On request

Part number	ØA	B	H1	H2	ØT	Swivel interference ØK	Load (kg)	Price each 1 to 5
RIM42-60/TCE	42	20	71	81	M8	84	60	44.77 €
RIM50-280/TCE	50	25	82	92	M12	101	280	71.10 €
RIM63-550/TCE	63	28	103	118	M12	125	550	96.62 €
RIM75-800/TCE	75	30	120	132	M16	142	800	106.81 €
RIM75-1000/TCE	75	30	120	132	M16	142	1000	127.36 €

Dimensions in mm

## Altri prodotti...



BPFL

Supporto a flangia ovale con cuscinetto, Lamiera



VCMB

Vite di giunzione metallo/legno, Acciaio




CDC

Molla di compressione conica, Conica



EMR

Volantino zigrinato a serraggio rapido, Zigrinato



PTR

Pignone tendicatena, Per applicazioni correnti



PFL

P-FLEX, Vite a pressione



CHM75

Riduttore a ruota e vite senza fine, fino a 298 Nm



UTKpwrr

Guida lineare Utilitrack®, Profilo guida a V




NKIA

Cuscinetto combinato con anello interno, Carico assiale



RFV40

Riduttore inox a ruota e vite senza fine, fino a 47 Nm



B

Ingranaggio conico - Acciaio 60C40, 1:1



GB-RA

Ingranaggio dritto ottone, Ottone CuZn39Pb3

## Prodotti correlati



RIMple

Ruota di livellamento, Con piastra



PDR-RD

Piede con ruota integrata, Ruota disassata