

Steel gravity rollers

For gravity
conveying systems

RLX/AC8

- Mounted on oiled conical steel bearings
- Moving individual loads
- Only for gravity applications
- Axle mounted on left side spring
- Materials:
 - Galvanised steel tube
 - Steel axle
 - Polypropylene roller housing
 - Polypropylene seals




Uses

- Maximum conveyor speed: 0.3 m/s
- Working temp range: -5 to +40 °C

Advantages

- Gentle lateral movement of the product being transported
- Design includes protection of bearing against dust and liquids
- Dirt resistant



RL = Useful length
EL = Installed length
AGL = Overall length

DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number	ØD roller	Tube thickness	ØA axle	RL	EL	AGL	F	Load capacity (N)	Stock*	Price each 1 to 5
RLX50-300/AC8	50	1,5	8	300	310	326	11	350	✓	11,38 €
RLX50-350/AC8	50	1,5	8	350	360	376	11	350	-	12,21 €
RLX50-400/AC8	50	1,5	8	400	410	426	11	350	-	13,06 €
RLX50-450/AC8	50	1,5	8	450	460	476	11	350	-	13,88 €
RLX50-500/AC8	50	1,5	8	500	510	526	11	350	-	14,71 €
RLX50-550/AC8	50	1,5	8	550	560	576	11	350	✓	15,55 €
RLX50-600/AC8	50	1,5	8	600	610	626	11	350	✓	16,36 €
RLX50-650/AC8	50	1,5	8	650	660	676	11	350	✓	17,20 €
RLX50-700/AC8	50	1,5	8	700	710	726	11	350	-	18,01 €
RLX50-750/AC8	50	1,5	8	750	760	776	11	350	-	18,85 €

Dimensions in mm

0 825 88 6000
Service 0,15 € / min
+ prix appel

Fax

cial2@hpcurope.com

HPC

SUPPLEMENT 2019


251

Altri prodotti...



BSPM

Vite a ricircolo di sfere
miniatura, Dado +
vite a ricircolo di sfere



M1

Coppia ruota e vite
senza fine, Plastica
lavorata (delrin)



TBEBASE10

Economic mini-table
with trapezoidal
leadscrew, 1kg



MET

Cuscinetto cilindrico,
Bronzo
autolubrificante
METAFRAM



HLUMss

Impugnatura girevole,
Inox 316



BH02

Cuscinetto radiale
flangiato, Montaggio
con circlips



PCH

Impugnatura, Fungo



SSB

Ingranaggio conico
inox, 1:1




MCL

Manicotto cilindrico
maschiato, Cilindrico -



CPAS-H

Squadra pieghevole,
Per carico pesante



GPLss

Scovolo, inox



ACL-FPA

Accessori per pannelli,
Morsetto angolare

Prodotti correlati



RLX

Rullo folle plastica,
PVC



GAL48_OMNI

Ruota per
trasportatore,
Omnidirezionale



PRF_BP

Maniglia e battuta per
porta, Arresto per
porta a battente