For gravity conveying systems

RLX/AC8




- ***Mounted on oiled conical steel bearings***
- *Moving individual loads*
- *Only for gravity applications*
- *Axle mounted on left side spring*
- *Materials:*
  Galvanised steel tube
  Steel axle
  Polypropylene roller housing
  Polypropylene seals

Uses

- *Maximum conveyor speed: 0.3 m/s*
- *Working temp range: -5 to + 40 ° C*

Advantages

- *Gentle lateral movement of the product being transported*
- *Design includes protection of bearing against dust and liquids*
- *Dirt resistant*



RL =Useful length
EL = Installed length
AGL = Overall length

DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number	ØD roller	Tube thickness	ØA axle	RL	EL	AGL	F	Load capacity (N)	Stock*	Price each 1 to 5
RLX50-300/AC8	50	1,5	8	300	310	326	11	350	✔	11,38 €
RLX50-350/AC8	50	1,5	8	350	360	376	11	350	-	12,21 €
RLX50-400/AC8	50	1,5	8	400	410	426	11	350	-	13,06 €
RLX50-450/AC8	50	1,5	8	450	460	476	11	350	-	13,88 €
RLX50-500/AC8	50	1,5	8	500	510	526	11	350	-	14,71 €
RLX50-550/AC8	50	1,5	8	550	560	576	11	350	✔	15,55 €
RLX50-600/AC8	50	1,5	8	600	610	626	11	350	✔	16,36 €
RLX50-650/AC8	50	1,5	8	650	660	676	11	350	✔	17,20 €
RLX50-700/AC8	50	1,5	8	700	710	726	11	350	-	18,01 €
RLX50-750/AC8	50	1,5	8	750	760	776	11	350	-	18,85 €

Dimensions in mm

Altri prodotti...



Ruota per vite senza fine , Bronzo



Rinvio angolare, fino a 4.4 Nm



Rullo tendicinghia, Per applicazioni correnti



Cerniera ad avvitare, 138 gradi



Chiusura a farfalla a molla, Tolleranze di montaggio ampie



Puleggia dentata di trasmissione tipo HTD, HTD5 Acciaio o alluminio



Anello di sollevamento,



Pignone a catena dentatura temprata, 12.7mm (DIN08B-1)



Braccio di reazione, Braccio di reazione per riduttori CHB



Ingranaggio dritto di precisione, Inox 303



Chiusura ¼ di giro per bloccaggio , Manopola plastica o inox



Stem support for caster, For swivel caster with central hole

Prodotti correlati



Rullo folle plastica, PVC



Ruota per trasportatore, Omnidirezionale



Maniglia e battuta per porta, Arresto per porta a battente