Ste Sta Pressed steel articulated foot Ø150

Accepts loads up to 40,000N

PTA150
PTA150ss


- **Levelling foot**
- Brilliant finish (Sand-blasted finish for base of the stainless steel version)
- Materials:

Steel version:
Base: Chromed steel sheet C40
Rod: Chromed steel (nut not supplied)
Sole: Vulcanised rubber NBR hardness 80° Shore

Stainless steel version:
Base: 304 stainless steel, brilliant or sand-blasted finish
Rod: 304 stainless steel (nut not supplied)
Sole: Vulcanised rubber NBR hardness 80° Shore

Sand-blasted stainless-steel version





Options

- Other rod sizes are available

DISCOUNTS

Qty	1+	15+	20+	25+	40+
Disc.	List	-5%	-10%	-15%	On request

Part number bright	Part number sanded finish	ØD	ØF	B	A	A/F	G	H	Static load (N)	Price each 1 to 14
Steel foot										
PTA150-24-100	-	150	M24	100	44	24	35	144	40000	52,69 €
PTA150-24-150	-	150	M24	150	44	24	35	194	40000	55,61 €
PTA150-24-200	-	150	M24	200	44	24	35	244	40000	58,77 €
PTA150-24-250	-	150	M24	250	44	24	35	294	40000	61,72 €
PTA150-30-100	-	150	M30	100	44	30	35	145	40000	57,84 €
PTA150-30-150	-	150	M30	150	44	30	35	195	40000	59,65 €
PTA150-30-200	-	150	M30	200	44	30	35	245	40000	65,66 €
PTA150-30-250	-	150	M30	250	44	30	35	395	40000	73,95 €
Stainless steel foot										
PTA150-24-100/SS	PTA150-24-100/SS/SB	150	M24	100	49	20	35	149	40000	72,32 €
PTA150-24-150/SS	PTA150-24-150/SS/SB	150	M24	150	49	20	35	199	40000	76,29 €
PTA150-24-200/SS	PTA150-24-200/SS/SB	150	M24	200	49	20	35	249	40000	80,27 €
PTA150-24-250/SS	PTA150-24-250/SS/SB	150	M24	250	49	20	35	299	40000	84,26 €
PTA150-30-100/SS	PTA150-30-100/SS/SB	150	M30	100	50	26	35	150	40000	82,29 €
PTA150-30-150/SS	PTA150-30-150/SS/SB	150	M30	150	50	26	35	200	40000	88,11 €
PTA150-30-200/SS	PTA150-30-200/SS/SB	150	M30	200	50	26	35	250	40000	93,00 €
PTA150-30-250/SS	PTA150-30-250/SS/SB	150	M30	250	50	26	35	300	40000	97,86 €

All dimensions in mm

Altri prodotti...


KB_WW

Manicotto chiuso a sfere di precisione, Economica


DOMI120

Accessori di collegamento, Piastra


RJA11_27

Guarnizione in gomma, Diverso dall'aggancio


PRF-SRA

Sistema di chiusura per profili alluminio, Serruta


SSG05


Spur gear with clamp, Stainless steel 303


CHA_GC_9SS

Cerniera (tutto inox), A saldare


RCC_RCX

Rondella sferica - DIN6319, concava


PTA80

Piede snodato con base stampata Ø80, 10000N



TBV

Tavola di posizionamento verticale manuale,


WS20

Binario Drylin® W, Binario


PRF4590_E

Squadra di giunzione, PRF4590


ASH

Anello di sollevamento, dritto a saldare

Prodotti correlati


PTA150

Piede snodato con base stampata Ø150, 40000N


PTA150

Piede snodato con base stampata Ø150, 40000N


PTA100

Piede snodato con base stampata Ø100, 15000N